


REV. W

DO NOT SCALE
FROM THIS PRINT

DIMENSIONS ARE IN INCHES		UNLESS OTHERWISE NOTED	TOLERANCES ARE:	TITLE:	DWG NO:
ONE PLACE DECIMALS $\pm .1$	THREE PLACE DECIMALS $\pm .005$		ANGLES $\pm 2^\circ$	DUAL ROW .050 x .050 STRIP ASSEMBLY	FLE-1XX-XX-XX-DV-X
TWO PLACE DECIMALS $\pm .01$	FOUR PLACE DECIMALS $\pm .0020$				SHEET 1 OF 2



NOTES:

1. MINIMUM PUSHOUT FORCE: .5 lb.
2. COPLANARITY; POS -2 THRU -26: .004
POS -27 THRU -75: .006
3. $\odot$ REPRESENTS A CRITICAL DIMENSION.
4. PACKAGE POSITIONS -05 THRU -75 IN TUBES; LAYER
PACKAGE POSITIONS -02 THRU -04.
5. FOR EVERY FINISHED PART, ONE POSITION WILL BE LOST
WHEN CUTTING BODY TO LENGTH.
6. BURR ALLOWANCE: .003 [.08] MAX.
7. CUT FLASH TO BE .010 [.25] MAX WITH NO FLASH
ALLOWED IN HOLES OR EXTENDING BELOW LEADS.

PROPRIETARY NOTE

THIS DOCUMENT CONTAINS INFORMATION
CONFIDENTIAL AND PROPRIETARY TO
SAMTEC INC. AND SHALL NOT BE
REPRODUCED OR TRANSMITTED TO
OTHER DOCUMENTS OR DISCLOSED TO
OTHERS OR USED FOR ANY PURPOSE
OTHER THAN THAT FOR WHICH IT WAS
OBTAINED WITHOUT THE EXPRESSED
WRITTEN CONSENT OF SAMTEC INC.

PLOT SCALE: .175/ DIMSCALE: .200

samtec

520 PARK EAST BLVD. NEW ALBANY, INDIANA 47150
PHONE (812) 944-6733 P.O. BOX 1147
CODE 55322

MADE BY: D PURVIS 11-05-96 FLE-1XX-XX-XX-DV-X
SHEET 1 OF 2