




This document is the property of and embodies
CONFIDENTIAL and PROPRIETARY information of FCI.
No part of the information shown on this
document may be used in any way or disclosed
to others without the written consent of FCI.
Copyright FCI.



PRODUCT NUMBER
SEE SHEET 2



mat'l code SEE NOTE 1				tolerances unless otherwise specified		CUSTOMER		FCI	
ltr	ecn no.	dr	date	linear	0.X ± 0.3	COPY	projection	www.fciconnect.com	
L	V06-0498	DCH	2006-05-30		0.XX ± 0.10			title	
M	V08-0124	HTB	2008-03-17		0.XXX ± 0.050			VERTICAL SIGNAL HDR. 6 ROW	
-	-	-	-	angles	0° ± 2°	MM	scale	product family	
G	V04-0070	DAI	2004-01-04	dr	S. KLINE	2000-04-21		METRAL 3000	
H	V04-0422	DAI	2004-05-06	enrg	J. ORTEGA	2000-04-20		code	
J	V04-0661	TAB	2004-06-22	chr	A. RAISTRICK	2000-04-21	2:1	size	
K	V05-0925	DAI	2005-10-24	appd	J. ORTEGA	2000-04-21		dwg no	
sheet		revision	M	M	M	M	M	A	
index		sheet	1	2	3	4	5	63372	
								213	
								1 of 5	

cage code 22526

Pro/E


PDM: Rev:M

STATUS: Released

Printed: Dec 01, 2010



PRODUCT NUMBER SEE NOTE 8	CONTACT PLATING PERFORMANCE LEVEL	PRESS FIT TAIL PLATING	DIM "A"	DIM "B" SIGNAL	DIM "B" GROUND	DIM "C"
63372-101	TELCORDIA CO	STANDARD (SnPb)	5.00	4.30	4.30	7.00
63372-101LF	TELCORDIA CO	LEAD FREE (Sn)	5.00	4.30	4.30	7.00
63372-102	TELCORDIA CO	STANDARD (SnPb)	5.75	4.30	4.30	7.00
63372-102LF	TELCORDIA CO	LEAD FREE (Sn)	5.75	4.30	4.30	7.00
63372-103	TELCORDIA CO	STANDARD (SnPb)	6.50	4.30	4.30	7.00
63372-103LF	TELCORDIA CO	LEAD FREE (Sn)	6.50	4.30	4.30	7.00
63372-104	TELCORDIA CO	STANDARD (SnPb)	5.00	4.30	4.30	6.25
63372-104LF	TELCORDIA CO	LEAD FREE (Sn)	5.00	4.30	4.30	6.25
63372-110	TELCORDIA CO	STANDARD (SnPb)	5.00	3.40	3.40	7.00
63372-110LF	TELCORDIA CO	LEAD FREE (Sn)	5.00	3.40	3.40	7.00
63372-111	TELCORDIA CO	STANDARD (SnPb)	5.75	3.40	3.40	7.00
63372-111LF	TELCORDIA CO	LEAD FREE (Sn)	5.75	3.40	3.40	7.00
63372-112	TELCORDIA CO	STANDARD (SnPb)	6.50	3.40	3.40	7.00
63372-112LF	TELCORDIA CO	LEAD FREE (Sn)	6.50	3.40	3.40	7.00
63372-114	TELCORDIA CO	STANDARD (SnPb)	5.00	3.40	3.40	6.25
63372-114LF	TELCORDIA CO	LEAD FREE (Sn)	5.00	3.40	3.40	6.25

mat'l code SEE NOTE 1				tolerances unless otherwise specified		CUSTOMER		 www.fciconnect.com		
ltr	ecn no.	dr	date	linear	0.X ±0.3	projection		title VERTICAL SIGNAL HDR. 6 ROW P.F. 30 PAIR SPECIAL LOAD		
M					0.XX ±0.10					
					0.XXX ±0.050					
				angles	0° ±2°					
				dr	S. KLINE 2000-04-21	 MM scale 1:1	product family METRAL 3000		code	
				enrg	J. ORTEGA 2000-04-20		size	dwg no	213	
				chr	A. RAISTRICK 2000-04-21		A	63372	sheet	
				appd	J. ORTEGA 2000-04-21				2	
sheet	revision									
index	sheet									

cage code 22526

Pro/E

PDM: Rev:M

STATUS: Released

Printed: Dec 01, 2010

1.35 TYP → | ←

1.30 TYP → | ←



PRODUCT NUMBER
SEE SHEET 2

SUGGESTED GROUND
CLEARANCE PATTERN

Ø 1.057
PAD SIZE

Ø 0.70 TYP
DRILLED HOLE
FINISHED HOLE
Ø 0.60 ± 0.05

0.127 0.127 0.127

OPTION A (EDGE COUPLED)
METRAL - HB DIFFERENTIAL
PCB TRACE LAYOUT

- 0.127 mm [0.005 in] TRACES MAX
WITH 0.127 mm [0.005 in] GAPS
- 4 TRACES (2 PAIRS) PER LAYER

Ø 1.057
Ø 0.70 TYP
DRILLED HOLE
FINISHED HOLE
Ø 0.60 ± 0.05

LAYER II
TRACES

LAYER I
TRACES

0.16 0.16 0.305

OPTION B (BROADSIDE COUPLED)
METRAL - HB DIFFERENTIAL
PCB TRACE LAYOUT

- UP TO 0.305 mm [0.012 in]
TRACES MAX WITH 0.16 mm
[0.006 in] GAPS
- 2 TRACES PER LAYER

mat'l code SEE NOTE 1				tolerances unless otherwise specified		CUSTOMER		FCI www.fciconnect.com	
ltr	ecn no.	dr	date	linear	0.X ± 0.3	projection	COPY	title	VERTICAL SIGNAL HDR. 6 ROW P.F. 30 PAIR SPECIAL LOAD
M					0.XX ± 0.10				
					0.XXX ± 0.050				
				angles	0° ± 2°	MM 2:1	scale	product family	METRAL 3000
				dr	S. KLINE 2000-04-21				
				enr	J. ORTEGA 2000-04-20				
				chr	A. RAISTRICK 2000-04-21	A	size	dwg no	63372
				appd	J. ORTEGA 2000-04-21				
sheet index	revision sheet								
								cage code	22526

This document is the property of and embodies
CONFIDENTIAL and PROPRIETARY information of FCI.
No part of the information shown on this
document may be used in any way or disclosed
to others without the written consent of FCI.
Copyright FCI.




PRODUCT NUMBER
SEE SHEET 2

NOTES:

- ①. BODY MATERIAL: LIQUID CRYSTAL POLYMER 30% GF
FLAME RETARDANT PER UL 94-V0.
PIN MATERIAL: COPPER ALLOY
- ②. DIM "C" REFERENCES GROUND PIN AND DIM "A" REFERENCES SIGNAL PIN
3. PRODUCT MARKING: PART NUMBER AND BATCH ID.
- ④. REFERENCE METRAL 3000 APPLICATION SPEC GS-20-012
FOR APPLICATION AND REPAIR REQUIREMENTS
- ⑤. DIMENSIONS AFTER INSERTION INTO CIRCUIT BOARD WITH
FCI APPROVED TOOLING.
6. REFERENCE METRAL 3000 PRODUCT SPEC GS-12-138
7. PRODUCTS WHERE THE PART NUMBER ENDS IN "LF"
MEETS EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY
REGULATIONS AS DESCRIBED IN GS-22-008.

ALL PRODUCTS WILL WITHSTAND EXPOSURE TO 260° C FOR 60 SECONDS
IN A CONVECTION, INFRA-RED OR VAPOR PHASE REFLOW OVEN.

- ⑧. FOR LEAD FREE PART NUMBERS ADD "LF" SUFFIX.
EXAMPLE: 63372-1YYLF.
- ⑨. COMPANY LOGO TO BE LOCATED IN THIS AREA.

mat'l code SEE NOTE 1				tolerances unless otherwise specified		CUSTOMER		 www.fciconnect.com			
ltr	ecn no.	dr	date	linear	0.X ±0.3		COPY		projection 	title VERTICAL SIGNAL HDR. 6 ROW P.F. 30 PAIR SPECIAL LOAD	
M					0.XX ±0.10						
					0.XXX ±0.050						
				angles	0° ±2°						
				dr	S. KLINE	2000-04-21	MM ←→		product family METRAL		code
				enrg	J. ORTEGA	2000-04-20			size	dwg no	213
				chr	A. RAISTRICK	2000-04-21			scale	63372	sheet
				appd	J. ORTEGA	2000-04-21	1:1		A	5	
sheet	revision										
index	sheet										

This document is the property of and embodies
CONFIDENTIAL and PROPRIETARY information of FCI.
No part of the information shown on this
document may be used in any way or disclosed
to others without the written consent of FCI.
Copyright FCI.