





D

C


B

A


- 1 WIRE RANGE: 0.12–0.9mm² (26–18 AWG).
- 2 INSULATION RANGE: 1.27–2.92 [.050–.115] MAX. DIA.
- 3 DIMENSIONS IN BRACKETS ARE IN INCHES.
- 4 PLATE INTERNALLY WITH 0.00076 [.000030] MIN GOLD IN THE LOCALIZED GOLD PLATE AREA, GOLD FLASH ON THE REMAINDER, OVER 0.00127 [.000050] MIN NICKEL UNDERPLATE.



SECTION A–A
SCALE 10:1



SECTION B–B
SCALE 10:1



SECTION C–C
SCALE 10:1

4 GOLD STRIPE	0.20 [.008] PHOS BRZ	641294–2
PRE–TIN	0.20 [.008] PHOS BRZ	641294–1
FINISH	MATERIAL	PART NO

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN K. SALMON 9–28–94	TE Connectivity	
DIMENSIONS: mm [INCHES]		CHK R. SWING 9–28–94	NAME MR RECEPTACLE	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		PRODUCT SPEC	RESTRICTED TO	
0 PLC ± –		APPLICATION SPEC	SIZE A1	
1 PLC ± –		WEIGHT	CAGE CODE 00779	
2 PLC ± –		CUSTOMER DRAWING	DRAWING NO 641294	
3 PLC ± 0.13 [.005]		SCALE 5:1	SHEET 1 OF 1	
4 PLC ± – ± –		REV E2		

