

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [87914-1616](#)
Status: **Active**
Overview: [C-Grid® Products](#)
Description: 2.54mm Pitch C-Grid® Header, Through Hole, Dual Row, Vertical, 16 Circuits, 2.50µm Tin (Sn) Overall Plating, Tray Packaging, Lead-Free

Documents:

[3D Model](#) [Product Specification PS-87920-019 \(PDF\)](#)
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

UL E29179

General

Product Family PCB Headers
Series [87914](#)
Application Board-to-Board, Signal, Wire-to-Board
Overview [C-Grid® Products](#)
Product Name C-Grid®

Physical

Breakaway Yes
Circuits (Loaded) 16
Circuits (maximum) 16
Color - Resin Black
First Mate / Last Break No
Flammability 94V-0
Glow-Wire Compliant No
Guide to Mating Part No
Keying to Mating Part None
Lock to Mating Part None
Mated Height 5.84mm
Material - Metal Copper Alloy
Material - Plating Mating Tin
Material - Plating Termination Nickel
Material - Resin High Temperature Thermoplastic
Number of Rows 2
Orientation Vertical
PC Tail Length 2.79mm
PCB Locator No
PCB Retention None
PCB Thickness - Recommended 1.60mm
Packaging Type Tray
Pitch - Mating Interface 2.54mm
Pitch - Termination Interface 2.54mm
Plating min - Mating 2.540µm
Plating min - Termination 1.270µm
Polarized to Mating Part No
Polarized to PCB No
Shrouded No
Stackable No
Surface Mount Compatible (SMC) Yes
Temperature Range - Operating -55°C to +105°C
Termination Interface: Style Through Hole

Electrical




image - Reference only

Series

EU RoHS

**ELV and RoHS
Compliant**

REACH SVHC

Not Reviewed

Low-Halogen Status

Not Reviewed

China RoHS



**Need more information on product
environmental compliance?**

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of
Compliance, [click here](#)

Please visit the [Contact Us](#) section for any
non-product compliance questions.

Search Parts in this Series

[87914Series](#)

Mates With

7859 Shunts, 71850 C-Grid® PCB
Receptacles, 70450 SL™ IDT Housing

Current - Maximum per Contact

3A

Voltage - Maximum

250V



Solder Process Data

Duration at Max. Process Temperature (seconds)

12

Lead-free Process Capability

Wave Capable (TH only)

Max. Cycles at Max. Process Temperature

1

Process Temperature max. C

260

Material Info

UPC

822348867769

Reference - Drawing Numbers

Product Specification

PS-87920-019

Sales Drawing

SD-87914-013

This document was generated on 07/12/2012

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

