

1.68 DISTANCE FROM COG TO
CENTER OF PICK UP ZONE

- R0.85
4X

7.50

3.30

$$-0.55$$
$$2X$$

△1 MATERIALS AND FINISH:
 -HOUSING AND COVER: THERMOPLASTIC, COLOR: NATURAL
 -CONTACTS: COPPER ALLOY, FINISH: Sn OVER Ni
 -HOLD DOWN: COPPER ALLOY, FINISH: Sn OVER Ni

2. MUST COMPLY WITH DIRECTIVE 2002/95/EC (ROHS)


3. NOTE DELETED.

△4 TO BE USED WITH UL1007 WIRE 22-18AWG SOLID,
20-18 AWG BONDED, 18 AWG STRANDED.


5. PACKAGED IN TAPE AND REEL

△ TO BE USED WITH UL1007 WIRE 26-24 AWG SOLID.

△7 DIMENSION SHOWN IS RECOMMENDED SOLDER MASK OPENING



2213189-1, -3



2213189-2, -4

VIEW E
(ROTATED 90° CW)

2.10

- 4.00

1.55

10.25


ALL CONTACTS AND
HOLD DOWN

SEE VIEW E

2213189-1, -2

26-24	Ø 2.50	WITH COVER		2213189-4
22-18	Ø 3.00	WITH COVER		2213189-3
26-24	Ø 2.50	W/O COVER		2213189-2
22-18	Ø 3.00	W/O COVER		2213189-1
MARKING	DIM X	DESCRIPTION	WIRE RANGE	PART NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 25OCT2012 CHK C.DAILY C.GINGRICH 25OCT2012		 TE Connectivity	
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ±.2 1 PLC ±0.2 2 PLC ±0.15 3 PLC ±. 4 PLC ±. ANGLES ±2A° FINISH		NAME ASSEMBLY, POKE-IN INVERTED THROUGH BOARD -	
		PRODUCT SPEC 108-32040 APPLICATION SPEC 114-32054		SIZE CAGE CODE DRAWING NO A2 00779 C=2213189	
MATERIAL -		WEIGHT -		RESTRICTED -	
CUSTOMER DRAWING				SCALE 6:1 SHEET 1 OF 4 REV A	



THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION20

© COPYRIGHT 20BY -ALL RIGHTS RESERVED.


LOC	DIST	REVISIONS				
		P	LTR	DESCRIPTION	DATE	DWN
		-		SEE SHEET 1	-	-

D



C

B


A





MOUNTING PCB LAYOUT
SCALE 12:1



2213189-1, -3
SCALE 10:1



WIRE PREPARATION DETAIL
SCALE 10:1



2213189-2, -4
SCALE 10:1

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN C. DAILY 25OCT2012	TE Connectivity			
DIMENSIONS: mm		CHK C. GINGRICH 25OCT2012				
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD -	NAME ASSEMBLY, POKE-IN INVERTED THROUGH BOARD			
0 PLC ± 1 PLC ±0.2 2 PLC ±0.15 3 PLC ± 4 PLC ± ANGLES ±2A° FINISH		PRODUCT SPEC 108-32040 APPLICATION SPEC 114-32054 WEIGHT -	SIZE A200779			
MATERIAL -		Customer Drawing	DRAWING NO C-2213189			
		SCALE 2:1	SHEET 3 OF 4			
			REV A			



D

C


B

A


LOC		DIST		REVISIONS					
P	LTR	DESCRIPTION				DATE	DWN	APVD	
	-	SEE SHEET 1				-	-	-	



SECTION B-B



SECTION A-A



REELING DIRECTION

PACKAGING FOR 2213189-1 SHOWN

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN C. DAILY 25OCT2012	TE Connectivity			
		CHK C. GINGRICH 25OCT2012				
DIMENSIONS:		APVD -	NAME ASSEMBLY, POKE-IN INVERTED THROUGH BOARD			
mm		PRODUCT SPEC 108-32040				
		APPLICATION SPEC 114-32054				
MATERIAL		WEIGHT -	SIZE A200779	CAGE CODE C-2213189	DRAWING NO.	RESTRICTED TO
		Customer Drawing	SCALE 2:1	SHEET 4 OF 4	REV A	