

Ultrasoft Recovery Rectifier Diode

PRODUCT APPLICATIONS



- Anti-Parallel Diode
 - Switchmode Power Supply
 - Inverters
- Applications
 - Induction Heating
- Resonant Mode Circuits
 - ZVS and ZCS Topologies
 - Phase Shifted Bridge

PRODUCT FEATURES

- Ultrasoft Recovery Times (t_{rr})
- Popular TO-247 Package or Surface Mount D³PAK Package
- Ultra Low Forward Voltage
- Low Leakage Current

PRODUCT BENEFITS

- Soft Switching - High Q_{rr}
- Low Noise Switching
 - Reduced Ringing
- Higher Reliability Systems
- Minimizes or eliminates snubber



1 - Anode 1
 2 - Common Cathode
 Back of Case - Cathode
 3 - Anode 2

MAXIMUM RATINGS

All Ratings per leg: $T_C = 25^\circ\text{C}$ unless otherwise specified.

Symbol	Characteristic / Test Conditions	Ratings	Unit
V_R	Maximum D.C. Reverse Voltage	600	Volts
V_{RRM}	Maximum Peak Repetitive Reverse Voltage		
V_{RWM}	Maximum Working Peak Reverse Voltage		
$I_{F(AV)}$	Maximum Average Forward current ($T_C = 126^\circ\text{C}$, Duty Cycle = 0.5)	30	Amps
$I_{F(RMS)}$	RMS Forward Current (Square wave, 50% duty)	51	
I_{FSM}	Non-Repetitive Forward Surge Current ($T_J = 45^\circ\text{C}$, 8.3 ms)	320	
T_J, T_{STG}	Operating and Storage Junction Temperature Range	-55 to 175	$^\circ\text{C}$
T_L	Lead Temperature for 10 Seconds	300	

STATIC ELECTRICAL CHARACTERISTICS

Symbol	Characteristic / Test Conditions		Min	Typ	Max	Unit
V _F	Forward Voltage	I _F = 30A		1.25	1.6	Volts
		I _F = 60A		2.0		
		I _F = 30A, T _J = 125°C		1.25		
I _{RM}	Maximum Reverse Leakage Current	V _R = 600V			25	µA
		V _R = 600V, T _J = 125°C			250	
C _T	Junction Capacitance, V _R = 200V			31		pF

DYNAMIC CHARACTERISTICS

APT30DL60BCT(G)

Symbol	Characteristic / Test Conditions	Min	Typ	Max	Unit
t_{rr}	Reverse Recovery Time $I_F = 1A, di_F/dt = -100A/\mu s, V_R = 30V, T_J = 25^\circ C$		64		ns
t_{rr}	Reverse Recovery Time		317		
Q_{rr}	Reverse Recovery Charge		962		nC
I_{RRM}	Maximum Reverse Recovery Current		7		Amps
t_{rr}	Reverse Recovery Time		561		ns
Q_{rr}	Reverse Recovery Charge		2244		nC
I_{RRM}	Maximum Reverse Recovery Current		9		Amps
t_{rr}	Reverse Recovery Time		264		ns
Q_{rr}	Reverse Recovery Charge		3191		nC
I_{RRM}	Maximum Reverse Recovery Current		26		Amps

THERMAL AND MECHANICAL CHARACTERISTICS

Symbol	Characteristic / Test Conditions	Min	Typ	Max	Unit
$R_{\theta JC}$	Junction-to-Case Thermal Resistance			1.00	$^\circ C/W$
W_T	Package Weight		0.22		oz
			5.9		g
Torque	Maximum Mounting Torque			10	lb-in
				1.1	N-m

Microsemi reserves the right to change, without notice, the specifications and information contained herein.




FIGURE 1a. MAXIMUM EFFECTIVE TRANSIENT THERMAL IMPEDANCE, JUNCTION-TO-CASE vs. PULSE DURATION




FIGURE 1b. TRANSIENT THERMAL IMPEDANCE MODEL

TYPICAL PERFORMANCE CURVES

APT30DL60BCT(G)




FIGURE 2, Forward Current vs. Forward Voltage




FIGURE 4, Reverse Recovery Charge vs. Current Rate of Change




FIGURE 6, Dynamic Parameters vs. Junction Temperature




FIGURE 8, Junction Capacitance vs. Reverse Voltage




FIGURE 3, Reverse Recovery Time vs. Current Rate of Change




FIGURE 5, Reverse Recovery Current vs. Current Rate of Change






FIGURE 7, Maximum Average Forward Current vs. Case Temperature

- 1 I_F - Forward Conduction Current
- 2 di_F/dt - Rate of Diode Current Change Through Zero Crossing.
- 3 I_{RRM} - Maximum Reverse Recovery Current.
- 4 t_{rr} - Reverse Recovery Time, measured from zero crossing where current goes from positive to negative, to the point at which line through I_{RRM} and $0.25 \cdot I_{RRM}$ passes through zero.



- 6 di_M/dt - Maximum Rate of Current Increase During the Trailing Portion of t_{rr} .

TO-247 (BCT) Package Outline



Dimensions in Millimeters and (Inches)