




LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
FT	47						
			P	REVISED PER ECO-12-012320	05JUL12	KH	MZ



- 1

0.76μm [.000030] MIN GOLD PER MIL-G-45204 ON MATING END FOR A LENGTH OF 5.08 [.200] MIN WITH 1.27μm [.000050] MIN MATTE TIN PLATE IN WIRE CRIMP AREA, BOTH OVER 0.76μm [.000030] MIN NICKEL PER QQ-N-290.
- 2

0.76μm [.000030] MIN GOLD PER MIL-G-45204 ON MATING END FOR A LENGTH OF 5.08 [.200] MIN WITH A UNIFORM GRADIENT TO 0.25μm [.000010] MIN GOLD PER MIL-G-45204 ON THE REMAINDER OVER 0.76μm [.000030] MIN NICKEL PER QQ-N-290.
- 3

0.38μm [.000015] MIN GOLD PER MIL-G-45204 ON MATING END FOR A LENGTH OF 5.08 [.200] MIN WITH 1.27μm [.000050] MIN MATTE TIN PLATE IN WIRE CRIMP AREA, BOTH OVER 0.76μm [.000030] MIN NICKEL PER QQ-N-290.
- 4

1.27μm [.000050] MIN TIN-LEAD PER MIL-T-10727 OVER 0.76μm [.000030] MIN NICKEL PER QQ-N-290.
- 5

GOLD PLATING NEED NOT APPEAR IN THIS AREA.
- 6

WIRE RANGE 24-20 AWG.
INSULATION RANGE 2.03 [.080]-2.54 [.100].
- 7

0.38μm [.000015] MIN GOLD PER MIL-G-45204 ON MATING END FOR A LENGTH OF 5.08 [.200] MIN, 1.27μm [.000050] MIN TIN-LEAD PER MIL-T-10727 FOR A LENGTH OF 5.69 [.224] MIN ON OPPOSITE END, BOTH OVER 1.27μm [.000050] MIN NICKEL PER QQ-N-290 ON ENTIRE CONTACT.
- 8

1.27μm [.000050] MIN TIN PER MIL-T-10727 OVER 0.76μm [.000030] MIN NICKEL PER QQ-N-290.
- 9

OBSELETE PARTS: OBSELETE CIS STREAMLINING PER D.RENAUD/D.SINISI

	SMALL PACK	8	1-66399-0	1-66399-1
	STANDARD	8	1-66331-4	1-66399-0
	SMALL PACK	1	66331-4	66399-9
9	OBSELETE	3	66331-7	66399-8
9	OBSELETE	2	66331-2	66399-7
	SMALL PACK	4	66331-1	66399-6
	STANDARD	7	1-66331-2	66399-5
	STANDARD	1	66331-4	66399-4
	STANDARD	3	66331-7	66399-3
	STANDARD	2	66331-2	66399-2
	STANDARD	4	66331-1	66399-1
	PACKAGING TYPE	BODY FINISH	STRIP P/N REF	PART NO
THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 7-30-91 R.SHIREY	TE Connectivity	
DIMENSIONS: mm [INCHES]		CHK 9-19-91 R.STONE		
		APVD 9-20-91 J.ESTMAN	NAME	
		PRODUCT SPEC		
		APPLICATION SPEC	SIZE CAGE CODE DRAWING NO	
MATERIAL		FINISH		
SEE CALLOUTS		SEE CALLOUTS	A2 00779 C=66399	
		WEIGHT	RESTRICTED TO	
		CUSTOMER DRAWING	SCALE 8:1 SHEET 1 of 1 REV P	