

Technical Specifications



Battery Charger:	Class 2, Power Supply
Plug:	AC/DC Adapter Wall Plug
Battery Type/Fit:	NiMH: 1-8 AA/HR6, 1-8 AAA/HR03, 1-4 C/HR14, 1-4 D/HR20, 9V
Typical Weight:	599 g
Input:	100-240V AC, 50/60 Hz, 8W
Output:	AA/HR6 450 mA, AAA/HR03 450 mA, C/HR14 450 mA, D/HR13 450 mA, 9V 32 mA
Operating Temp:	0°C - 35°C (32°F - 95°F)
Dimensions:	203 mm (H) x 108 mm (W) x 60 mm (D)

BENEFITS

Simple & Easy to Use "All-In-One" Charger for Multiple Cell Sizes
4 AA/AAA ready in 3 hrs.*

FEATURES

Charges AA, AAA, C, D, 9V NiMH cells-LED Indicates Charge Status

- Amber LED for AA, AAA, C, D, 9V
- Charges up to 8 cells at the same time
- Charges multiple sizes at once

LED Indicates Charge

- Red LED for 9V
- Solid Red = Charging
- Green = Complete
- Flashing Red = Error/Abnormal battery or abnormal temperature

Charger Automatically detects cell sizes at the same time

International Charge Capability- device can be used worldwide with suitable converter plug

SAFETY

Microprocessor Controlled

- Charge Termination based on -dV/dt, temperature, and/or built in timer
- Primary Cell Protection- will not charge non-rechargeable batteries
- Over-temperature shut off- prevents overheating of cell
- Over-charge protection- prevents cell damage
- Low-voltage battery protection- prevents overheating and damage to cell
- Power protection circuit- resets whenever a battery is removed

DURACELL
BATTERIES

Berkshire Corporate Park
Bethel, CT 06801 U.S.A.
Tel: Toll free 1.800.544.5454
Web: www.duracell.com

*Charge rate and time is dependent on cell capacity, discharge state, and operating temperature.

Information and contents in this data sheet are for reference purposes only. They do not constitute any warranty and representation is subject to change without notice. For most current information and further details, please contact Duracell.