

Miniature Fuse, 10.3 x 38 mm, Quick-Acting F, 250 VAC



250 VAC · Quick-Acting F



NNO

Description

- Low Breaking Capacity

References

This type is Phase-out without alternate type
Last order date: 20.02.2012


Weblinks

[pdf-datasheet](#), [html-datasheet](#), [General Product Information](#), [Approvals](#), [CE declaration of conformity](#), [RoHS](#), [CHINA-RoHS](#), [REACH](#), [e-Shop](#), [SCHURTER-Stock-Check](#), [Distributor-Stock-Check](#), [Detailed request for product](#)

Technical Data

Rated Voltage	250 VAC
Rated current	0.4 - 30 A
Breaking Capacity	100 A - 4000 A
Characteristic	Quick-Acting F
Mounting	Fuseholder / Clip
Admissible Ambient Air Temp.	-40 °C to 70 °C
Climatic Category	40/070/56 acc. to IEC 60068-1
Material: Terminals	Nickel-Plated Copper Alloy
Material: Tube	Glass
Material: Endcaps	Nickel-Plated Copper
Unit Weight	9 g
Storage Conditions	0 °C to 60 °C, max. 70% r.h.
Product Marking	Rated current

Dimension




Pre-Arcing Time

Rated Current In 1.1 x In min. 1.3 x In max. 3.0 x In max.

0.4 A - 30 A	60 min	60 min	1 s
--------------	--------	--------	-----

Time-Current-Curves



Packaging Unit Small Box Pack (10 pcs.)