


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

	PART NO.	MATERIAL	MARKER SIZE inches [mm]	LABELS PER ROW	STANDARD PKG. QTY.
	C080X020YJT	GMY2	0.800 X 0.200 [20.3] X [5.08]	3	10000
2	C080X020KBT	GMK 4			
2	C080X020KCT				
	C080X020CBT	GMC			



NOTE :

NOTE:
1. SEE MFG. DWG. NO. A61227.
2. MILLIMETER ARE IN [].

CAD FILENAME/LAYERS 100472HG_C10264_C080X020xxT_01.PRT											
									PANDUIT CORP. TINLEY PARK, ILLINOIS CUSTOMER DRAWING OPTIMUM C080X020YJT, C080X020KBT C080X020KCT AND C080X020CBT THERMAL TRANSFER LABELS		
									UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: (.X) ± .031 (.XXX) ± .010 (.XX) ± .015 ANGLES ±	UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJECTION.	
2	4/13/07	RVU		ADDED P/N: C080X020KCT. C080X020KBT, MATERIAL SHOULD BE GMK4.	4948	R			DRAWN BY RVU	MAT'L: SEE TABLE	SCALE NTS
1	3-31-06	RVU		ADDED "CUSTOMER DRAWING" ON TITLE. .800 WAS .850. .325 WAS .375	4435	R			DATE 9-30-04		DRAWING NO.
0	9-30-04	RVU		DRAWING RELEASE.	0000	R			CHK'D		C10264
REV	DATE	BY	CHK	DESCRIPTION	ECN	- R	CUST	SUP			DWG A SIZE