







16 radii without dimension $R=0.5$

25 CONTACT EJECT FORCE: NOTES

26 WITHOUT PINS IN SMALL CONNECTOR CAVITY.

15	TINNED	CuSn6	0.63mm TAB(EL)	21	30
14	TINNED	CuSn6	0.63mm TAB(L)	21	30
13	TINNED	CuSn6	0.63mm TAB(M)	21	30
12	TINNED	CuSn6	0.63mm TAB(S)	21	30
11	TINNED	CuSn6	1.5mm TAB(E.L)	1	7
10	TINNED	CuSn6	1.5mm TAB(L)	1	7
9	TINNED	CuSn6	1.5mm TAB(M)	1	7
8	TINNED	CuSn6	1.5mm TAB(S)	1	7
7	TINNED	CuSn6	2.8mm TAB(L)	2	2
6	TINNED	CuSn6	2.8mm TAB(M)	2	2
5	TINNED	CuSn6	2.8mm TAB(S)	2	2
4	NATURAL	PA66-GF50	JOINT HSG "B"	1	-
3	BLACK	PA66-GF50	JOINT HSG "A"	-	1
2	BLACK	PA66-GF30	HEADER HSG(94P)	1	-
1	BLACK	PA66-GF30	HEADER HSG(154P)	-	1
NO	FINISH/ COLOR	MATERIAL	DESCRIPTION	QTY FOR ASSY	


CUSTOMER DRAWING

SCALE 2:1

SHEET 1 OF 1

FOR

INFORMATION ONLY FOR P.C.B LAYOUT(94P)



CODING			Tyco ASS'Y drawing no.
	Modul 60	Modul 94	
Z	-	-	0-1897294-2
Z	-	-	1-1897294-2
C	2,3,6,7	10,11,14,15	TBD
D	2,4,6,8	10,12,14,16	TBD
E	1,3,6,8	9,11,14,16	TBD
F	2,4,5,7	10,12,13,15	TBD
G	2,3,5,8	10,11,13,16	TBD
H	1,4,6,7	9,12,14,15	TBD

PRODU
108.81

APPLIC

WEIGHT

•

Quic

CUSTOMER DRAWING

SCALE 2:1

SHEET 1 OF 1

FOR