




PROJEKT NO.

A98-52140

B909529

| LOC | DIST | REVISIONS |     |                     |           |     |      |
|-----|------|-----------|-----|---------------------|-----------|-----|------|
|     |      | P         | LTR | DESCRIPTION         | DATE      | DWN | APVD |
| A   | I    | -         | F   | SEE PCN E-06-023642 | 09OCT2006 | LG  | HSCH |
|     |      |           |     |                     |           |     |      |
|     |      |           |     |                     |           |     |      |

|                                  |              |                                                                        |
|----------------------------------|--------------|------------------------------------------------------------------------|
| 0-1355585-1/-2/-3                | 1            | AMPMODU II PINHEADER WITH SHORT CIRCUIT BRIDGE<br>18+4POS, COD A, 180° |
| 0-1241719-1                      | 1            | COVER WITH SLIDE, COD A, 90° CABLEOUTLET                               |
| AMP BESTELL-NR.<br>AMP ORDER NO. | STK.<br>QTY. | BENENNUNG<br>DESCRIPTION                                               |
| COUNTERPARTS<br>GEGENSTECKER     |              |                                                                        |



- NOTES  
BEMERKUNGEN
- 1

ORDER NUMBER  
BESTELL-NUMMER
- 2

REVISION NUMBER  
WERKZEUGÄNDERUNGSINDEX
- 3

MATERIAL MARKING  
WERKSTOFFKENNZEICHNUNG
- E


-

CUSTOMER SIGN  
KUNDEN-KÜRZZEICHEN
- 5

PACKAGING IN CARTON  
VERPACKUNG IN KARTON
- 6

PRODUCTION DATE  
PRODUKTIONSdatum
- 7

CAVITY MARKING  
NESTMARKIERUNG



1:1

|                                 |      |      |              |                          |          |                       |
|---------------------------------|------|------|--------------|--------------------------|----------|-----------------------|
| 0-1241726-1                     | F    | -    | 1            | MOS REC HSG,<br>18+4 POS | PBT GF15 | GELB<br>YELLOW ⑥      |
| AMP<br>BESTELL-NR.<br>ORDER NO. | REV. | POS. | STK.<br>QTY. | BENENNUNG<br>DESCRIPTION | MATERIAL | OBERFLÄCHE<br>SURFACE |
|                                 |      |      |              |                          |          | FARBE/COLOUR          |

|                    |                                                 |            |            |           |             |                                  |           |
|--------------------|-------------------------------------------------|------------|------------|-----------|-------------|----------------------------------|-----------|
| MOS-Buchsenkontakt | 0-963715-1                                      | 0-963729-1 | 0.75       | CuNiSi    | vorverzinnt | 878591-2                         | 734464-1  |
|                    | 0-928999-1                                      | 0-963726-1 | 0.35-0.5   | CuNiSi    | vorverzinnt | 878439-2                         | 734237-2  |
| Kontakte           | AMP Bestell-Nummer<br>Bandware Einzelausführung |            | DGB in mm² | Werkstoff | Oberflaeche | Crimp-Werkzeuge<br>Masch.-Werkz. | Handzange |

|                                                                                       |  |                                                                                 |  |                            |                                           |               |
|---------------------------------------------------------------------------------------|--|---------------------------------------------------------------------------------|--|----------------------------|-------------------------------------------|---------------|
| DIMENSIONS:                                                                           |  | TOLERANCES UNLESS OTHERWISE SPECIFIED:                                          |  | DWN<br>H. Schmitt 23JUN99  | AMP Deutschland GmbH                      |               |
| mm                                                                                    |  | 0 PLC ±0.3<br>1 PLC ±0.3<br>2 PLC ±0.3<br>3 PLC ±0.3<br>4 PLC ±0.3<br>ANGLES ±° |  | CHK<br>V. Berkmann 10JAN01 | D - 63225 Langen                          |               |
|  |  | PRODUCT SPEC<br>108-18687                                                       |  | APVD<br>-                  | NAME<br>MOS RECEPTACLE HOUSING<br>18+4POS |               |
| MATERIAL<br>-                                                                         |  | APPLICATION SPEC<br>114-18332                                                   |  | SIZE<br>A                  |                                           | RESTRICTED TO |
| FINISH<br>-                                                                           |  | WEIGHT<br>-                                                                     |  | DRAWING NO<br>00779        |                                           | REV F         |
| CUSTOMER DRAWING                                                                      |  |                                                                                 |  | SCALE 5:1 SHEET 1 OF 1     |                                           |               |