

1



**RAD18-183**  
nylon self-insulated  
installing tools – WT145C,  
WT2000, ERG-2001,  
ERG-2003, WT112M

2



**18RAD-183**  
vinyl self-insulated  
installing tools – WT145C,  
WT2000, ERG-2001,  
ERG-2003, WT112M

3



**18RAD-18377**  
nylon fully-insulated  
installing tools – WT145C,  
WT2000, ERG-2001,  
ERG-2003, WT112M



**AD18-183**  
non-insulated  
installing tools –  
WT111M, ERG-2002,  
WT2000, WT112M,

5



**RAD18-187A**  
nylon fully-insulated 90° flag  
installing tools – WT1145C,  
WT2000, ERG-2001,  
ERG-2003, WT112M

*Disconnect terminals provide a quick, reliable method of connection to terminal blocks and boards without the use of tools. They are supplied in a variety of styles to meet virtually all quick-disconnect requirements. Female disconnect terminals and matching male tabs accommodate a range of 22-10 AWG, and are available in non-insulated, partially insulated, and fully insulated styles, in both nylon and vinyl. They are available in various tab widths including .250", .187", and .110", and a combination size. A unique construction of the female disconnect offers long-term dependability.*


### 187 Series – Female Disconnects

	Cat. No.	Pkg. Qty.	Tab Size	Wire Range	Max. Ins. Dia.	Dimensions	
						A	B
1	<b>RAD18-183</b>	100	.187 x .032	22-18	.136	.83	.23
	<b>RAD1833</b>	1000	.187 x .032	22-18	.136	.83	.23
	<b>RAD18-182</b>	100	.187 x .020	22-18	.136	.83	.23
	<b>RAD1823</b>	1000	.187 x .020	22-18	.136	.83	.23
	<b>RBD14-183</b>	100	.187 x .032	16-14	.163	.83	.23
	<b>RBD1833</b>	1000	.187 x .032	16-14	.163	.83	.23
	<b>RBD14-182</b>	100	.187 x .020	16-14	.163	.83	.23
	<b>RBD1823</b>	1000	.187 x .020	16-14	.163	.83	.23
2	<b>18RAD-183</b>	100	.187 x .032	22-18	.150	.85	.23
	<b>RAD1837</b>	1000	.187 x .032	22-18	.150	.85	.23
	<b>18RAD-182</b>	100	.187 x .020	22-18	.150	.85	.23
	<b>RAD1827</b>	1000	.187 x .020	22-18	.150	.85	.23
	<b>14RBD-183</b>	100	.187 x .032	16-14	.170	.85	.23
	<b>RBD1837</b>	1000	.187 x .032	16-14	.170	.85	.23
	<b>14RBD-182</b>	100	.187 x .020	16-14	.170	.85	.23
	<b>RBD1827</b>	1000	.187 x .020	16-14	.170	.85	.23
3	<b>18RAD-18377</b>	100	.187 x .032	22-18	.150	.89	.30
	<b>RAD18377</b>	1000	.187 x .032	22-18	.150	.89	.30
	<b>18RAD-18277</b>	100	.187 x .020	22-18	.150	.89	.30
	<b>RAD18277</b>	1000	.187 x .020	22-18	.150	.89	.30
	<b>14RBD-18377</b>	100	.187 x .032	16-14	.170	.89	.30
	<b>RBD18377</b>	1000	.187 x .032	16-14	.170	.89	.30
	<b>14RBD-18277</b>	100	.187 x .020	16-14	.170	.89	.30
	<b>RBD18277</b>	1000	.187 x .020	16-14	.170	.89	.30
4	<b>AD18-183</b>	100	.187 x .032	22-18	—	.64	.23
	<b>AD183</b>	1000	.187 x .032	22-18	—	.64	.23
	<b>AD18-182</b>	100	.187 x .020	22-18	—	.64	.23
	<b>AD182</b>	1000	.187 x .020	22-18	—	.64	.23
	<b>BD14-183</b>	100	.187 x .032	16-14	—	.64	.23
	<b>BD183</b>	1000	.187 x .032	16-14	—	.64	.23
	<b>BD14-182</b>	100	.187 x .020	16-14	—	.64	.23
5	<b>RAD18-187A</b>	50	.187 x .032	22-18	.150	.74	.59
	<b>RAD1877F</b>	500	.187 x .032	22-18	.150	.74	.59
	<b>RAD18-188A</b>	50	.187 x .020	22-18	.150	.74	.59
	<b>RAD1887F</b>	500	.187 x .020	22-18	.150	.74	.59
	<b>RBD14-187A</b>	50	.187 x .032	16-14	.170	.74	.61
	<b>RBD1877F</b>	500	.187 x .032	16-14	.170	.74	.61
	<b>RBD14-188A</b>	50	.187 x .020	16-14	.170	.74	.61
	<b>RBD1887F</b>	500	.187 x .020	16-14	.170	.74	.61

U.L. Listed E66716

Material: brass

Finish: tin plated



*Most standard bulk catalog numbers can be put on Mylar Tape for reel fed applications (i.e. 12050 tool and application dies). See page 57 for description of tooling. Please add the suffix "M" for Mylar Tape (i.e. RA2573-M).*