




| O.P. (MM) | P.T. (MM) |
|-----------|-----------|
| 9.5 ±0.3  | 2.6 MAX   |

O.P. = OPERATING POINT  
P.T. = PRE-TRAVEL

NC 2      3 NO  
COM 1  
CIRCUIT: SPDT



ISOMETRIC



## NOTES:

1. ALL DIMENSIONS IN MM [INCH]
2. GENERAL TOLERANCE: X.X=±0.4  
X.XX=±0.25
3. RATING: 0.4VA @20V (AC or DC)
- ▲ 4. OPERATING FORCE: 10 ± 5 GRAMS
5. OPERATING TEMP: -25°C TO 85°C
6. ELECTRICAL LIFE: 50,000 CYCLES MIN.
7. MECHANICAL LIFE: 1,000,000 CYCLES TYP.
8. INSULATION RESISTANCE: 100 Mega-OHMS
9. DIELECTRIC STRENGTH: 1000VAC 1 MINUTE (INITIAL VALUE)
10. CONTACT RESISTANCE: 100 Milli-OHMS MAX.
- ▲ 11. CONTACTS: 10 MICRO INCHES MINIMUM GOLD PLATING (PN: Q990001)
12. ▲ DENOTES CRITICAL PARAMETER.
13. 2002/95/EC (ROHS) COMPLIANT



E-SWITCH®



TITLE MS085R103F010S1A

|     |        |                         |         |     |
|-----|--------|-------------------------|---------|-----|
| A   | 19257  | RELEASED FOR PRODUCTION | 8/23/10 | BLR |
| REV | PCR NO | DESCRIPTION             | DATE    | BY  |

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY  
TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED

SCALE 2:1

DATE 8/23/2010

DR BLR

DWG Q970113

REV A