



## Dual Pitch Professional Hole Saws

Featuring the smooth cutting action of our Constant Pitch hole saw, combined with aggressive material penetration and swarf clearance, Dual Pitch Professional hole saws will cut equally well on thin and thicker gauge materials. **This removes the need to carry a constant and a variable pitch hole saw.**

### Advantages:

- The complete multi purpose saw. Dual Pitch Professional saws will cut a wide range of materials, irrespective of thickness.
- Starrett designed tooth geometry resulting in huge improvements in chip flow.
- Smooth cut with minimal tendency to bite or snag when cutting thinner gauge materials.
- Cutting depth 41mm (1 5/8").
- A range of general purpose and specialist kits are available, featuring the most popular sizes of saw. Please see pages 11-12 for full details.

### Kits Available!



Please see page 11

### Dual Pitch Professional and Constant Pitch Bi Metal Hole Saw

#### Excellent Cutting Performance



Metal  
Inox (Stainless)



Non Ferrous Materials

#### Satisfactory Cutting Performance



Wood



Veneer



Formica



Plastic



Acrylic



Fibreglass



Plaster



Suspended Floors



## Constant Pitch Hole Saws

Like our Dual Pitch hole saw, the Constant Pitch provides a smooth cut, with minimal tendency to bite or snag on contact with irregular surfaces. Six teeth per 25mm/inch makes this saw ideal for thinner gauge materials.

### Kits Available!



Please see page 11

### Advantages:

- Smooth cut on thinner gauge materials.
- Minimal tendency to bite or snag on thinner gauge materials.
- Cutting depth 41mm (1 5/8").
- A range of general purpose and specialist kits are available, featuring the most popular sizes of saw. Please see pages 11-12 for full details.

| SAW SPECIFICATIONS |         |            |           |
|--------------------|---------|------------|-----------|
| DIAMETER           |         | DUAL PITCH | CON PITCH |
| MM                 | INCH    | CAT NO     | CAT NO    |
| 14                 | 9/16    | DH0096     | SH0096    |
| 16                 | 5/8     | DH0058     | SH0058    |
| 17                 | 11/16   | DH1016     | SH1016    |
| 19                 | 3/4     | DH0034     | SH0034    |
| 20                 | 25/32   | DH2532     | SH2532    |
| 21                 | 13/16   | DH1036     | SH1036    |
| 22                 | 7/8     | DH0078     | SH0078    |
| 24                 | 15/16   | DH1056     | SH1056    |
| 25                 | 1       | DH0100     | SH0100    |
| 27                 | 1.1/16  | DH0116     | SH0116    |
| 29                 | 1.1/8   | DH0118     | SH0118    |
| 30                 | 1.3/16  | DH0136     | SH0136    |
| 32                 | 1.1/4   | DH0114     | SH0114    |
| 33                 | 1.5/16  | DH0156     | SH0156    |
| 35                 | 1.3/8   | DH0138     | SH0138    |
| 37                 | 1.7/16  | DH0176     | SH0176    |
| 38                 | 1.1/2   | DH0112     | SH0112    |
| 40                 | 1.9/16  | DH0196     | SH0196    |
| 41                 | 1.5/8   | DH0158     | SH0158    |
| 43                 | 1.11/16 | DH1116     | SH1116    |
| 44                 | 1.3/4   | DH0134     | SH0134    |
| 46                 | 1.13/16 | DH1136     | SH1136    |
| 48                 | 1.7/8   | DH0178     | SH0178    |
| 51                 | 2       | DH0200     | SH0200    |
| 52                 | 2.1/16  | DH0216     | SH0216    |
| 54                 | 2.1/8   | DH0218     | SH0218    |
| 56                 | 2.3/16  | DH56MM     | SH56MM    |
| 57                 | 2.1/4   | DH0214     | SH0214    |
| 59                 | 2.5/16  | DH0256     | SH0256    |
| 60                 | 2.3/8   | DH0238     | SH0238    |
| 64                 | 2.1/2   | DH0212     | SH0212    |
| 65                 | 2.9/16  | DH0296     | SH0296    |
| 67                 | 2.5/8   | DH0258     | SH0258    |
| 68                 | 2.11/16 | DH68MM     | SH68MM    |
| 70                 | 2.3/4   | DH0234     | SH0234    |
| 73                 | 2.7/8   | DH0278     | SH0278    |
| 76                 | 3       | DH0300     | SH0300    |
| 79                 | 3.1/8   | DH0318     | SH0318    |
| 83                 | 3.1/4   | DH0314     | SH0314    |
| 86                 | 3.3/8   | DH0338     | SH0338    |
| 89                 | 3.1/2   | DH0312     | SH0312    |
| 92                 | 3.5/8   | DH0358     | SH0358    |
| 95                 | 3.3/4   | DH0334     | SH0334    |
| 98                 | 3.7/8   | DH0378     | SH0378    |
| 102                | 4       | DH0400     | SH0400    |
| 105                | 4.1/8   | DH0418     | SH0418    |
| 108                | 4.1/4   | DH0414     | SH0414    |
| 111                | 4.3/8   | DH0438     | SH0438    |
| 114                | 4.1/2   | DH0412     | SH0412    |
| 121                | 4.3/4   | DH0434     | SH0434    |
| 127                | 5       | DH0500     | SH0500    |
| 133                | 5.1/4   | DH0514     | SH0514    |
| 140                | 5.1/2   | DH0512     | SH0512    |
| 152                | 6       | DH0600     | SH0600    |
| 160                | 6.5/16  | DH160MM    | SH160MM   |
| 168                | 6.5/8   | DH168MM    | SH168MM   |
| 177                | 6.31/32 | DH177MM    | SH177MM   |
| 210                | 8.9/32  | DH210MM    | SH210MM   |