





JKL LAMP NUMBER	VOLTS RATED	WATTS	INITIAL MSCP	INITIAL LUMENS	AVERAGE LIFE HRS.	FILAMENT TYPE
6S6-12V	12	6	3.58	45.0	1,500	C-2V
6S6-30V	30	6	3.98	50.0	1,500	C-2V
6S6-120V	120	6	3.18	40.0	1,500	C-7A
6S6-145V	145	6	3.18	40.0	1,500	C-7A
6S6-155V	155	6	3.18	40.0	1,500	C-7A
10S6-230V	230	10	5.97	75.0	1,500	C-1
10S6-250V	250	10	5.97	75.0	1,500	C-1

METRIC



THIRD ANGLE PROJECTION

DIMENSIONS ARE IN MILLIMETERS

TOLERANCE UNLESS OTHERWISE SPECIFIED

1 PL +/- 0.2

2 PL +/- 0.20

ANGLE +/- 0

DRAWN BY
L. WENGSTROM

APPVD BY DATE
Q.C. 3/1/01

JKL

COMPONENTS CORPORATION

TITLE

S-6 MINIATURE CANDELABRA
SCREW BASE LAMP

DRAWN BY
L. WENGSTROM

APPVD BY DATE
Q.C. 3/1/01

SIZE
A

FSCM NO.
55335

DRAWING NO.

SCREW BASE CANDELABRA S-6

- CAD DRAWING -
MANUAL REVISIONS NOT PERMITTED

SCALE

NONE

RELEASED DATE

3/1/01

REVISION DATE

REV. NO.

SHEET

1 OF 1

REV. NO.	DESCRIPTION/ECO NUMBER	APPVD DATE