

MATERIALS AND FINISHES





(73366-0030/73366-0031)
FRONT BODY BRASS
PLATED NICKEL

(73366-0032)
FRONT BODY BRASS
PLATED GOLD

CENTER CONTACT BERYLLIUM COPPER
PLATED GOLD

INSULATOR TEFLON

HOUSING ZINC ALLOY
PLATED TIN



RECOMMENDED MOUNTING PATTERN

73366-0036	73366-0032 PACKED BY TRAY (54CAV.)
73366-0035	73366-0030 PACKED ONE PER BAG
73366-0034	73366-0031 SMALL TRAY
73366-0033	73366-0030 SMALL TRAY
73366-0032	TAPE & REEL
73366-0031	GENERAL
73366-0030	GENERAL
PART NO.	PACKAGING DESCRIPTION

PS-89675-1830	PRODUCT SPECIFICATION
SPECIFICATION	DESCRIPTION

CHG: ADD -0036
PER PDR14051612
EC NO: URF2014-0664
2014/05/21
DRW:LIN
CHKD:
APPR:MHUANG
2014/06/05
REV

QUALITY SYMBOLS
▽=0
▽=0

GENERAL TOLERANCES (UNLESS SPECIFIED)

	mm	INCH
4 PLACES	$\pm .004$	$\pm .001$
3 PLACES	$\pm .005$	$\pm .001$
2 PLACES	$\pm .006$	$\pm .001$
1 PLACE	$\pm .007$	$\pm .001$

ANGULAR $\pm 2^\circ$

DRAFT WHERE APPLICABLE
MUST REMAIN
WITHIN DIMENSIONS

DIMENSION STYLE
MM/IN

DRAWN BY
LYNN

CHECKED BY
PENNY

APPROVED BY
MISEN

DATE
2000/02/10

DATE
2000/02/10

DATE
2000/02/10

SEE NOTES

SCALE
DESIGN UNITS
METRIC


TITLE
MCX JACK R/A PCB 50 OHM
MCX-J/RA/PCB

MOLEX INCORPORATED

DOCUMENT NO.
SD-73366-003


SHEET NO.
1 OF 3

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION



NOTE:

1. 10 PITCHES CUMULATIVE TOLERANCE ± 0.20(.008)



SECTION A-A

CHG: SEE SHEET 1
EC NO: URF2014-0664
DRWN: LIN 2014/05/21
CHKD: APPR: MUANG 2014/06/05
REV

QUALITY SYMBOLS
=0
=0

GENERAL TOLERANCES (UNLESS SPECIFIED)

	mm	INCH
4 PLACES	± .005	± .0002
3 PLACES	± .004	± .00015
2 PLACES	± .003	± .0001
1 PLACE	± .002	± .00008

ANGULAR ± 2 °

DRAFT WHERE APPLICABLE
MUST REMAIN
WITHIN DIMENSIONS

DIMENSION STYLE
MM/IN

DRAWN BY	DATE
LYNN	2000/02/10

CHECKED BY	DATE
PENNY	2000/02/10

APPROVED BY	DATE
MISEN	2000/02/10

SEE SHEET 1

SCALE
DESIGN UNITS
METRIC


THIRD ANGLE PROJECTION

TITLE
MCX JACK R/A PCB 50 OHM
MCX-J/RA/PCB

MATERIAL NO.
DOCUMENT NO.
SD-73366-003

SHEET NO.
2 OF 3

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION



CHG: SEE SHEET 1
EC NO: URF2014-0664
2014/05/21
DRWN: LIN
CHKD: C7
APPR: HUANG
2014/06/05

QUALITY
SYMBOLS
▽=0
▽=0

GENERAL TOLERANCES
(UNLESS SPECIFIED)

	mm	INCH
4 PLACES	± .---	± .---
3 PLACES	± .---	± .---
2 PLACES	± .---	± .---
1 PLACE	± .---	± .---

ANGULAR ± 2 °

DRAFT WHERE APPLICABLE
MUST REMAIN
WITHIN DIMENSIONS

DIMENSION STYLE
MM/IN

DRAWN BY	DATE
LYNN	2000/02/10

CHECKED BY	DATE
PENNY	2000/02/10

APPROVED BY	DATE
MISEN	2000/02/10

MATERIAL NO.
SEE SHEET 1

SCALE
METRIC

DESIGN UNITS
METRIC

THIRD ANGLE
PROJECTION

TITLE
MCX JACK R/A PCB 50 OHM
MCX-J/RA/PCB

MOLEX INCORPORATED

DOCUMENT NO.
SD-73366-003

SHEET NO.
3 OF 3

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX
INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION