

## Model 73084, 73085, 73086, 73088

Terminal Jacks, Male Threads 6-32, 8-32, 10-32, Female Threads 10-32

### Features

- Adapter provides an easy and quick banana jack connection by replacing the screw in a terminal strip or control panel.
- Allows a standard sheathed or unsheathed banana plug / patch cord to securely connect to a terminal strip.
- Helps to avoid accidental arc-over by eliminating the usage of alligator clips, or test probe "slip offs" during measurement applications.
- Perfect for use with model **73087** jumper test lead sets in *peer-checking system* test sequences.
- *For more information, please visit our "**Articles**" section on nuclear applications at [www.pomonaelectronics.com](http://www.pomonaelectronics.com).*



### Materials

Banana Jack: Nickel-plated Brass  
Insulation: Polypropylene V-2


### Specifications

Voltage:	600 Vrms, Maximum voltage for <i>hands free use</i> . For <i>CE compliance</i> , do not hold in hand when voltages exceed 33 Vrms / 70 Vdc
Current:	20 A
Operating Temperature:	-10° C to +80° C (+14° F to 176° F)
Torque In/Lb.:	
<b>73084:</b>	7
<b>73085:</b>	20
<b>73086:</b>	20
<b>73088:</b>	16

### Dimensions



**Model 73086, 10-32 Female Terminal Jack**



**USA:** Sales: 800-490-2361  
Technical Support: [technicalsupport@pomonatest.com](mailto:technicalsupport@pomonatest.com)  
Fax: 425-446-5844


**Europe:** 31-(0) 40 2675 150 **International:** 425-446-5500  
**Where to Buy:** [www.pomonaelectronics.com](http://www.pomonaelectronics.com)

All dimensions are in inches. Tolerances (except noted): .xx = ±.02" (.51 mm), .xxx = ± .005" (.127 mm). All specifications are to the latest revisions. Specifications are subject to change without notice. Registered trademarks are the property of their respective companies.


**Model 73084, 73085, 73086, 73088**  
Terminal Jacks, Male Threads 6-32, 8-32, 10-32, Female Threads 10-32




**Model 73084, 6-32 Male Terminal Jack**



**Model 73088, 8-32 Male Terminal Jack**



**Model 73085, 10-32 Male Terminal Jack**



## Ordering Information

Model: **73084, 73085, 73086, 73088**

Standard Colors: -0 Black, -2 Red, -4 Yellow, -6 Blue

Ordering Example: **73084-2**, (73084 terminal jack with Red insulation)

**USA:** Sales: 800-490-2361

Technical Support: [technicalsupport@pomonatest.com](mailto:technicalsupport@pomonatest.com)

Fax: 425-446-5844

**Europe:** 31-(0) 40 2675 150 **International:** 425-446-5500

**Where to Buy:** [www.pomonaelectronics.com](http://www.pomonaelectronics.com)

All dimensions are in inches. Tolerances (except noted): .xx =  $\pm .02"$  (.51 mm), .xxx =  $\pm .005"$  (.127 mm). All specifications are to the latest revisions. Specifications are subject to change without notice. Registered trademarks are the property of their respective companies.

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Pomona:

[73088-4](#) [73086-4](#) [73088-0](#) [73086-0](#) [73086-6](#) [73086-2](#) [73084-6](#) [73085-4](#) [73084-0](#) [73084-4](#) [73085-0](#) [73088-2](#)  
[73084-2](#) [73085-6](#) [73088-6](#) [73085-2](#)