





ウエハー
WAFER
ナイロン66, UL94V-2
NYLON66,

ピン (□ 1.14X25.4)
黄銅, 銅下地錫メッキ
BRASS, TIN OVER COPPER PLATING



注記
NOTE

- 1 全極数が偶数の場合のみ適用。
TO BE APPLIED ONLY WHEN ALL CKTS. ARE EVEN.
- 2 ウエハーの反りは、長さ 25.4 に対して 0.2 最大。
CAMBER MUST BE 0.2 MAX. PER 25.4.



59.88	55.88	10-33-1121	5280-12A	12
44.64	40.64	↑ -1091	↑ -09A	9
39.56	35.56	↑ -1081	↑ -08A	8
34.48	30.48	↑ -1071	↑ -07A	7
29.4	25.4	↑ -1061	↑ -06A	6
24.32	20.32	↑ -1051	↑ -05A	5
19.24	15.24	↑ -1041	↑ -04A	4
14.16	10.16	↑ -1031	↑ -03A	3
9.08	5.08	10-33-1021	5280-02A	2
B	A	EDP NO.	ENG. NO.	極数 CKT.

材料 MATERIAL		図中参照 SEE DRAWING		molex MOLEX-JAPAN CO.,LTD. 日本モレックス株式会社	
仕上げ FINISH		—		REVISE ONLY ON CAD SYSTEM	
適用電線範囲 WIRE RANGE		—		TITLE 名称	
被覆外径 INS. RANGE		—		KK 5.08 WAFER ASS'Y	
DRAWN BY %/4/9 T.YASUI		CHK'D BY %/4/10 S.A.M.FUKUSHIMA		DWG. NO.	
APP'D BY %/4/10 M.FUKUSHIMA		尺 度 SCALE		SD-5280-NA	
角度 ANGLE		±3°		REV	
30 以上 OVER		±0.3		B	
10 以上 30 未満 OVER UNDER		±0.25			
10 未満 UNDER		±0.2			
一般公差 GENERAL TOLERANCES		記号 LTR		変更内容 REVISION RECORD	
		DR. CHK.		日付 DATE	