





PRODUCT NUMBER	SERIES NAME	PITCH
20020010-CXXXXXXLF	02-350	3.50 mm



2p to 6p with wedge, above 7p
without wedge (including 7p)






N = Number of poles
Dim A = $N \times 3.5$ [.138]
Dim B = $(N-1) \times 3.5$ [.138]

POLES	TOLERANCE
2-6p	± 0.15 [.006]
7-12p	± 0.20 [.008]
13-18p	± 0.25 [.010]
19-24p	± 0.30 [.012]


mat'l. code				surface ASME Y14.5 ✓	tolerance ASME Y14.5	projection MM [INCH]	product family TERMINAL BLOCK
ltr	ecn no	dr	date	tolerances unless otherwise specified			title
F				angles X $\pm 1^\circ$	X ± 0.5 X.X ± 0.3 X.XX ± 0.1	scale	TERMINAL BLOCK PLUGGABLE PLUG, BACK SIDE HOOK
		dr	JASON HSU	120909			dwg no
		enr	JASON HSU	120909			sheet 2 of 5 size
		chr	GARY HSIEH	120909			20020010
		appd	JOSEPH HSIA	120909			A4
sheet index	revision sheet						type
							CUSTOMER Drawing

PRODUCT NUMBER	SERIES NAME	PITCH
20020010-DXXXXXXLF	02-381	3.81 mm






N = Number of poles
 Dim A = $N \times 3.81$ [.150]
 Dim B = $(N-1) \times 3.81$ [.150]

POLES	TOLERANCE
2-6p	± 0.15 [.006]
7-12p	± 0.20 [.008]
13-18p	± 0.25 [.010]
19-24p	± 0.30 [.012]





mat'l. code				surface ASME Y14.5 ✓	tolerance ASME Y14.5	projection MM [INCH]	product family TERMINAL BLOCK
ltr	ecn no	dr	date	tolerances unless otherwise specified			title
F				angles	X.±0.5 X.X±0.3		TERMINAL BLOCK
				X*±1°	X.XX±0.1	scale	PLUGGABLE PLUG, BACK SIDE HOOK
		dr	JASON HSU	120909		FCI	dwg no
		enr	JASON HSU	120909			sheet 3 of 5 size
		chr	GARY HSIEH	120909			20020010
		appd	JOSEPH HSIA	120909			A4
sheet index	revision sheet						type
							CUSTOMER Drawing

PRODUCT NUMBER	SERIES NAME	PITCH
20020010-GXXXXXXLF	02-500	5.00 mm



N = Number of poles
Dim A = $N \times 5.0$ [.197]
Dim B = $(N-1) \times 5.0$ [.197]




POLES	TOLERANCE
2-6p	± 0.15 [.006]
7-12p	± 0.25 [.010]
13-18p	± 0.30 [.012]
19-24p	± 0.40 [.016]



SECTION P-P


mat'l. code				surface ASME Y14.5	tolerance ASME Y14.5	projection MM [INCH]	product family TERMINAL BLOCK
ltr	ecn no	dr	date	tolerances unless otherwise specified			title
F				angles	X.±0.5		TERMINAL BLOCK
				linear	X.X±0.3		PLUGGABLE PLUG, BACK SIDE HOOK
				X*±1°	X.XX±0.1	scale	dwg no
		dr	JASON HSU	120909		FCI	sheet 4 of 5
		enr	JASON HSU	120909			20020010
		chr	GARY HSIEH	120909			A4
		appd	JOSEPH HSIA	120909			type
sheet index	revision sheet						CUSTOMER Drawing

PRODUCT NUMBER	SERIES NAME	PITCH
20020010-HXXXXXXLF	02-508	5.08 mm




N = Number of poles
Dim A = $N \times 5.08$ [.200]
Dim B = $(N-1) \times 5.08$ [.200]

POLES	TOLERANCE
2-6p	± 0.15 [.006]
7-12p	± 0.25 [.010]
13-18p	± 0.30 [.012]
19-24p	± 0.40 [.016]



SECTION P-P



mat'l. code				surface ASME Y14.5		tolerance ASME Y14.5		projection 		product family TERMINAL BLOCK											
ltr		ecn no		dr		date		tolerances unless otherwise specified				title									
F								angles				X.±0.5		MM		TERMINAL BLOCK					
								linear				X.X±0.3				PLUGGABLE PLUG, BACK SIDE HOOK					
								X'±1"				X.XX±0.1		scale							
								dr		JASON HSU		120909				dwg no		sheet 5 of 5		size	
								enrg		JASON HSU		120909				20020010		A4			
								chr		GARY HSIEH		120909									
								appd		JOSEPH HSIA		120909									
sheet index		revision sheet														type		CUSTOMER Drawing			