


MARKETING SALES DRAWING

DIMENSIONS IN INCHES - DO NOT SCALE THIS DRAWING


DIMENSIONS IN METRIC - []

This drawing is the property of Tusonix, Inc., and may not be used, reproduced, published or disclosed to others without expressed authorization by Tusonix Inc.


Electrical Testing
per Tusonix standard
test plans and Mil-Std-202
Test Methods.



ORIENTATION



CIRCUIT



NOTES:

1. TUSONIX PART NUMBER: 4101-504.
2. LEAD FINISH: 60/40 SOLDER PLATED.
3. EYELET FINISH: 60/40 SOLDER PLATED.

MIN. CAP. pF	85°C Working Voltage	Current IDC	Minimum No Load Insertion Loss (dB) at 25°C per Mil-Std-220			
			10 MHz	100 MHz	1 GHz	10 GHz
5500	200 VDC 200 VAC	10 A	15	55	70	70

X-2015 Rev-0	REVISION RECORD	Original Release C.O. 20080716-3-01	0		--TOLERANCES-- Unless Otherwise Specified	Title EMI FILTER M15733/51-0001	
					DECIMAL ± .031[0.79]		
					ANGLES ± 	Drawn S.M. 07-17-08	Scale 5 X
					TUSONIX TUCSON, ARIZONA	Approved R.L. 07-17-08	
						A	4101-504

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tusonix:](#)

[4101-504](#)