

+85°C General Purpose Surface Mount Aluminum Electrolytic Capacitors

Part Number: 106SML035MD4



This part is RoHS compliant

Electrical Specifications

Capacitance: 10 μ F

Tolerance: -20 %, +20 %

WVDC: 35 volts DC

SVDC: 44 volts DC

Dissipation Factor:
0.14 at 120 Hz, 20°C

Temperature Range:
-40°C to +85°C

Impedance:

Impedance Ratios:
-25°C/20°C - 2
-40°C/20°C - 4

ESR:
23.21 Ohms at 120 Hz and 20°C

Ripple Current:
27 mA at 120 Hz and 85°C

Leakage Current:
.03CV or 4 μ A, whichever is greater
3.5 μ A after 1 Minute

Load Life:
2000 Hours at 85°C with 100% of rated voltage and with 0% of rated ripple current

Frequency Multipliers

50 Hz	120 Hz	400 Hz	1 KHz	10 KHz	100 KHz
0.8	1	1	1.1	1.5	1.5

Temperature Multipliers

45°C	60°C	65°C	70°C	75°C	85°C	105°C	125°C
1.35	1.35	1.35	1.35	1	1	0	0

Physical Specifications

Diameter (D):	4 mm + 0.5 mm
Length (L):	5.4 mm + 0.2 mm
Pad Spacing(C):	5 mm +/- 0.2 mm
Lead Width (R):	0.5 mm to 0.8 mm
Lead Spacing (P):	1 mm +/- 0.2 mm
Pad Length(H):	4.3 mm +/- 0.2 mm
Pad Width(W):	4.3 mm +/- 0.2 mm

