





Product Number	Compliant Pin	Packaging
10122388-101LF	12 Places	Tray



3D VIEW
SCALE 1:1

NOTES:

1, DESCRIPTION	Q'ty	MATERIAL	PLATING
TOP CAGE	1PCS	NICKEL SILVER ALLOY T=0.25	NO PLATING
BOTTOM CAGE	1PCS	NICKEL SILVER ALLOY T=0.25	NO PLATING
MID CAGE	3PCS	NICKEL SILVER ALLOY T=0.25	NO PLATING
BACK CAGE	1PCS	NICKEL SILVER ALLOY T=0.25	NO PLATING
EMI SPRING	N/A	COPPER ALLOY T=0.08	Ni PLATED

2, PRODUCT SPECIFICATION: GS-12-1165





3, APPLICATION SPECIFICATION: GS-20-0384

4, PACKAGE PER GS-14-2344 AND GS-14-920


spec ref	RELEASE			dr	Art Lin	2014-01-09	projection	size	scale
tolerance std	TOLERANCES UNLESS OTHERWISE SPECIFIED			eng	Zhen Luo	2014-01-09		A4	1:1
ISO406				chr	Collins Lu	2014-01-10		ecn no	
ISO1101				appr	JEFFREY QIN	2014-01-10		rel level	Released
surface	linear	0.X	±0.25				product family		SFP+
		0.XX	±0.20						
		0.XXX	±0.15						
ISO1302	angular	0°	±0.5°	www.fci.com			cat. no.		-
							Product-Customer Drw		sheet 1 of 5

Pro/E File - REV C - 2009-06-09

Product Number	Compliant Pin	Packaging
10122388-201LF	Without	Tray



3D VIEW
SCALE 1:1



spec ref		RELEASE		dr	Art Lin	2014-01-09			size	scale		
tolerance std	TOLERANCES UNLESS OTHERWISE SPECIFIED			eng	Zhen Luo	2014-01-09			A4	1:1		
				chr	Collins Lu	2014-01-10			ecn no			
ISO406				appr	JEFFREY QIN	2014-01-10	product family		SFP+	rel level	Released	
ISO1101												
surface 	linear	0.X	±0.25		title	SFP+ 1X4 CAGE EMI SPRING TYPE PRESS FIT			dwg no	10122388		rev
		0.XX	±0.20									
		0.XXX	±0.15									
	angular	0°	±0.5°	www.fci.com								
ISO1302												


Proj/E File - REV C - 2009-06-09




Copyright FCI.




Copyright FCI.




RECOMMENDED BEZEL CUT-OUT SINGLE SIDED APPLICATIONS



RECOMMENDED BEZEL CUT-OUT BELLY TO BELLY APPLICATIONS



MOUNTED ON PC BOARD
SHOWN THRU RECOMMENDED BEZEL




MOUNTED BELLY TO BELLY ON PC BOARD
SHOWN THRU RECOMMENDED BEZEL


spec ref		RELEASE		dr	Art Lin	2014-01-09	projection	MM	size	scale			
tolerance std	TOLERANCES UNLESS OTHERWISE SPECIFIED			eng	Zhen Luo	2014-01-09			A4	1:1			
				chr	Collins Lu	2014-01-10			ecn no				
ISO406				appr	JEFFREY QIN	2014-01-10	product family	SFP+	rel level	Released			
ISO1101													
surface ISO1302	linear	0.X	±0.25		title	SFP+ 1X4 CAGE EMI SPRING TYPE PRESS FIT			dwg no	10122388		rev	C
		0.XX	±0.20										
		0.XXX	±0.15										
		angular	0°	±0.5°	www.fci.com	cat. no.	-	Product-Customer Drw			sheet 3 of 5		

Pro/E File - REV C - 2009-06-09

10122388-101LF
RECOMMENDED PCB CONFIGURATION
WITH KEEP-OUT AREAS
SINGLE SIDED APPLICATIONS





10122388-101LF
RECOMMENDED PCB CONFIGURATION
WITH KEEP-OUT AREAS
BELLY TO BELLY APPLICATIONS





spec ref		RELEASE		dr	Art Lin	2014-01-09	projection 		MM	size A4	scale 1:1
tolerance std ISO406 ISO1101	TOLERANCES UNLESS OTHERWISE SPECIFIED		eng	Zhen Luo	2014-01-09	ecn no					
			chr	Collins Lu	2014-01-10	rel level Released					
				appr	JEFFREY QIN	2014-01-10	product family SFP+				
surface ISO1302	linear	0.X	±0.25		title SFP+ 1X4 CAGE EMI SPRING TYPE PRESS FIT			dwg no 10122388	rev C		
		0.XX	±0.20								
		0.XXX	±0.15								
		angular	0°	±0.5°	www.fci.com	cat. no.		-	Product-Customer Drw		sheet 4 of 5

Proj/E File - REV C - 2009-06-09

10122388-201LF
RECOMMENDED PCB CONFIGURATION
WITH KEEP-OUT AREAS
SINGLE SIDED APPLICATIONS



10122388-201LF
RECOMMENDED PCB CONFIGURATION
WITH KEEP-OUT AREAS
BELLY TO BELLY APPLICATIONS



spec ref		RELEASE		dr	Art Lin	2014-01-09	projection 	 MM	size	scale		
tolerance std ISO406 ISO1101	TOLERANCES UNLESS OTHERWISE SPECIFIED		eng	Zhen Luo	2014-01-09	A4			1:1			
			chr	Collins Lu	2014-01-10	ecn no						
				appr	JEFFREY QIN	2014-01-10	product family		SFP+	rel level	Released	
surface  ISO1302	linear	0.X	±0.25		title SFP+ 1X4 CAGE EMI SPRING TYPE PRESS FIT				dwg no	10122388		rev C
		0.XX	±0.20									
		0.XXX	±0.15									
		angular	0°	±0.5°	www.fci.com	cat. no.		-	Product-Customer Drw			sheet 5 of 5

Proj/E File - REV C - 2009-06-09