






PRODUCT NUMBER
SEE TABLE



mat'l. code				surface		tolerance		projection		product family	
NOTES 1 & 5				ISO 1302		ISO 406		ISO 1101		HEADERS	
ltr	ecn no	dr	date	tolerances unless otherwise specified		linear		INCH/MM		title	
AD	BLX-14106	DCS	2013-02-06	angles		XX±.01/XX±0.3		scale 2:1		VERTICAL 2-ROW GUIDE PIN	
X	V81283	EPK	10/14/98	0°±2'		XXX±.005/XXX±0.13		FCI		(SLOTTED) HEADER-SOLDER TAILS	
Y	V03-0342	GJP	3/21/03	dr		S. ROYER		3/28/90		dwg no	
AA	M05-0089	MHT	5/16/05	engr		A. MCNEE		3/28/90		sheet 1 of 3	
AB	M07-0116	AGS	2/19/07	chr		A. MCNEE		3/28/90		67273	
AC	M09-0059	MHT	4/16/09	appd		A. MCNEE		3/28/90		type	
sheet	revision	AD	AD	AD		AD		AD		Product Customer Drawing	
index	sheet	1	2	3		3		3		A3	

PRODUCT NUMBER NOTE 4 & 7	SIZE NOTE 4	TAIL LENGTH DIM H	DIM D	DIM G	DIM E	OVERALL LENGTH DIM L	PLATING NOTE 10
67273-XXX	2 x XXX	.177/4.50	NOTE 3	.37/.94+DIM D	.40/10.2+DIM D	.48/12.2+DIM D	30u"/.76u Au OVER 50u"/1.27u Ni
67274-XXX		.177/4.50					15u"/.38u Au OVER 50u"/1.27u Ni
67275-XXX		.177/4.50					GOLD FLASH OVER 50u"/1.27u Ni
67276-XXX		.177/4.50					120u"/3.05u Sn OVER 50u"/1.27u Ni
68513-XXX		.122/3.10					30u"/.76u Au OVER 50u"/1.27u Ni
68581-XXX		.177/4.50					30u"/.76u GXT™ OVER 50u"/1.27u Ni
68839-XXX		.177/4.50					15u"/.38u GXT™ OVER 50u"/1.27u Ni
69291-XXX		.177/4.50					DUPLEX 15u"/.38u Au & 100u"/2.54u Sn OVER 50u"/1.27u Ni
69292-XXX		.177/4.50					DUPLEX 30u"/.76u Au & 100u"/2.54u Sn OVER 50u"/1.27u Ni
69695-XXX		.177/4.50					50u"/1.27u Au OVER 50u"/1.27u Ni
78580-XXX		.122/3.10					30u"/.76u GXT™ OVER 50u"/1.27u Ni
78942-XXX		.122/3.10					120u"/3.05u Sn OVER 50u"/1.27u Ni
78943-XXX		.122/3.10					15u"/.38u GXT™ OVER 50u"/1.27u Ni
78944-XXX		.122/3.10					15u"/.38u Au OVER 50u"/1.27u Ni
90350-XXX		.122/3.10					DUPLEX 30u"/.76u Au & 100u"/2.54u Sn OVER 50u"/1.27u Ni
95737-XXX	2 x XXX	.100/2.54	NOTE 3	.37/.94+DIM D	.40/10.2+DIM D	.48/12.2+DIM D	30u"/.76u GXT™ OVER 50u"/1.27u Ni

NOTES :

- MOLDING MATERIAL : HI-TEMP RESIN
PER UL 94 V-0 COLOR : NATURAL
- PIN RETENTION TO BE 3 LBS/1.36 KG
MIN PER PIN IN EITHER DIRECTION.
- DIM D =
(NO. OF COLUMNS-1) TIMES .100(ENGLISH)
(NO. OF COLUMNS-1) TIMES 2.54(METRIC)
- XXX REPRESENTS NO. OF COLUMNS
(i.e. 2 x 5 PART IS -005)
-001 THRU -004 ARE NOT AVAILABLE,
-005 THRU -050 ARE AVAILABLE.
- TERMINAL MATERIAL : 3/4/HARD PHOS BRONZE ALLOY
UNS C51000
- FLATNESS IS MEASURED FROM THE BOTTOM
OF THE END STANDOFFS.
- ADD "LF" SUFFIX AT THE END OF PART NUMBER FOR LEAD FREE OPTION.
- THE HOUSING WILL WITHSTAND EXPOSURE TO 260°C PEAK TEMPERATURE
FOR 15 SECONDS IN A WAVE SOLDER APPLICATION WITH A 1.5mm
MINIMUM THICK CIRCUIT BOARD. SEE APPLICATION NOTES/PROCEDURES
IF THEY ARE AVAILABLE.
- THESE PRODUCT MEETS EUROPEAN UNION DIRECTIVES AND OTHER
COUNTRY REGULATION AS DESCRIBED IN GS-22-008.
- PLATING OPTIONS:
MAY BE EITHER GOLD OR GXT PLATED AT MANUFACTURER'S OPTION.
- FOR 67273 SERIES PLATING OPTIONS:
-XXX=0XX,MAY BE EITHER GOLD OR GXT PLATED AT MANUFACTURER'S OPTION.
-XXX=GXX,GOLD PLATING ONLY

mat'l. code				surface		tolerance		projection		product family		
NOTES 1 & 5				ISO 1302 ✓		ISO 406 ISO 1101				HEADERS		
ltr	ecn	no	dr	date	tolerances unless otherwise specified					title		
AD					angles	linear	.XX±.01/.XX±.03 .XXX±.005/.XX±.013 .XXXX±.0020/.XXX±.005	INCH/MM		VERTICAL 2-ROW GUIDE PIN (SLOTTED) HEADER-SOLDER TAILS		
					0°±2°			scale 2:1		dwg no		
					dr	S. ROYER	3/28/90			sheet 2 of 3 size		
					enr	A. MCNEE	3/28/90			67273 A3		
					chr	A. MCNEE	3/28/90			type		
					appd	A. MCNEE	3/28/90			Product Customer Drawing		
sheet	revision											
index	sheet											

PRODUCT NUMBER NOTE 4 & 7	SIZE NOTE 4	TAIL LENGTH DIM H	DIM D	DIM G	DIM E	OVERALL LENGTH DIM L	PLATING	
67273-XXXLF	2 x XXX	.177/4.50	NOTE 3	.37/.94+DIM D	.40/10.2+DIM D	.48/12.2+DIM D	30u"/.76u Au OVER 50u"/1.27u Ni	SEE NOTE 11
67274-XXXLF		.177/4.50					15u"/.38u Au OVER 50u"/1.27u Ni	SEE NOTE 10
67275-XXXLF		.177/4.50					GOLD FLASH OVER 50u"/1.27u Ni	
67276-XXXLF		.177/4.50					100u"/2.54u PURE Sn OVER 50u"/1.27u Ni	
68513-XXXLF		.122/3.10					30u"/.76u Au OVER 50u"/1.27u Ni	
68581-XXXLF		.177/4.50					30u"/.76u GXT™ OVER 50u"/1.27u Ni	
68839-XXXLF		.177/4.50					15u"/.38u GXT™ OVER 50u"/1.27u Ni	
69291-XXXLF		.177/4.50					DUPLEX 15u"/.38u Au & 100u"/2.54u PURE Sn OVER 50u"/1.27u Ni	
69292-XXXLF		.177/4.50					DUPLEX 30u"/.76u Au & 100u"/2.54u PURE Sn OVER 50u"/1.27u Ni	
69695-XXXLF		.177/4.50					50u"/1.27u Au OVER 50u"/1.27u Ni	
78580-XXXLF		.122/3.10					30u"/.76u GXT™ OVER 50u"/1.27u Ni	
78942-XXXLF		.122/3.10					100u"/2.54u PURE Sn OVER 50u"/1.27u Ni	
78943-XXXLF		.122/3.10					15u"/.38u GXT™ OVER 50u"/1.27u Ni	
78944-XXXLF		.122/3.10					15u"/.38u Au OVER 50u"/1.27u Ni	
90350-XXXLF		.122/3.10					DUPLEX 30u"/.76u Au & 100u"/2.54u PURE Sn OVER 50u"/1.27u Ni	
95737-XXXLF	2 x XXX	.100/2.54	NOTE 3	.37/.94+DIM D	.40/10.2+DIM D	.48/12.2+DIM D	30u"/.76u GXT™ OVER 50u"/1.27u Ni	

mat'l. code NOTES 1 & 5				surface ISO 1302 ✓		tolerance ISO 406 ISO 1101		projection INCH/MM		product family HEADERS			
ltr		ecn no		dr		date		tolerances unless otherwise specified		title			
AD								linear		VERTICAL 2-ROW GUIDE PIN (SLOTTED) HEADER-SOLDER TAILS			
								0°±2'		scale 2:1			
						dr		S. ROYER		3/28/90			
						enr		A. MCNEE		3/28/90			
						chr		A. MCNEE		3/28/90			
						appd		A. MCNEE		3/28/90			
sheet index		revision sheet								sheet 3 of 3 size A3			
										type Product Customer Drawing			