

AN6454SH


Pager Direct Conversion FSK Demodulator Mixer IC

■ Overview

The AN6454SH supports direct conversion FSK demodulation for pagers, and incorporates two mixers.

■ Features


- Low current consumption : 1mA
- Incorporates two mixers. 450MHz input frequency.
- Small surface-mount package with 0.5mm pitch.



■ Pin Descriptions

Pin No.	Description	Pin No.	Description
1	MIX bias	6	MIX (2) output
2	L-OSC input (1)	7	MIX (1) output
3	L-OSC input (2)	8	GND
4	MIX current control	9	RF bias
5	V_{CC}	10	RF input

■ Functional Block Diagram



■ Absolute Maximum Ratings (Ta=25°C)

Parameter	Symbol	Rating	Unit
Supply voltage	V _{CC}	4	V
Supply current	I _{CC}	20	mA
Power dissipation	P _D	143.5 (Ta=75°C)	mW
Operating ambient temperature	T _{opr}	-20 to + 70	°C
Storage temperature	T _{stg}	-55 to +125	°C

Note) Protect pins 3, 9, and 10 from electrostatic discharge.

■ Recommended Operating Range

Parameter	Symbol	Range
Operating supply voltage range	V _{CC}	1.8 to 3V

■ Electrical Characteristics (V_{CC}=2.0V, Ta=25±2°C)





Parameter	Symbol	Condition	min	typ	max	Unit
Current consumption	I _{tot}		0.6	1.0	1.4	mA
MIX output level (1)	V _{MIX1}	Input Level -54dBm, f=450.0045MHz	-38	-34	-30	dBs
MIX output level (2)	V _{MIX1}	Input Level -54dBm, f=450.0045MHz	-38	-34	-30	dBs

■ Electrical Characteristics (Design Values for Reference) (V_{CC}=2.0V, Ta=25±2°C)

The following are design values for reference only (not guaranteed)

Parameter	Symbol	Condition	min	typ	max	Unit
RF bias voltage	V _{RF}		—	0.745	—	V
MIX bias current	V _{MIX}		—	1.3	—	V
MIX output level difference	D _{Vmix}	D _{Vmix} =V _{mix1} -V _{mix2}	-3.2	—	3.2	dB
Output noise level	V _{n3}	V _{n3} = $\sqrt{\frac{(Vn2)^2 + (Vn2)^2}{2}}$	—	—	25	dBs

■ Pin Descriptions

Pin No.	Symbol	Description	Equivalent circuit
1	MIX bias	Local oscillator bias. Normally grounded through a capacitor.	
2	L-OSC input 1	Local oscillator inputs to Pin 2 w and 3 are different in phase by $\pi/2$. These inputs are different in frequency by FM Dev from Pin 10 input.	
3	L-OSC input 2		
4	MIX-current control	Current input to this pin controls the IC's operation and total current. This pin may be connected to Pin 22 of AN6400.	
5	V _{CC}	This is the supply voltage pin.	—
6	MIX2 output	Direct-conversion mixer outputs (FM Dev.). These outputs are different in phase by $\pi/2$ from each other. These pins may be to AN6400 or other direct conversion demodulator ICs for data retrieval.	
7	MIX1 output		

■ Pin Descriptions (Cont.)

Pin No.	Symbol	Description	Equivalent circuit
8	GND	This is the ground pin.	—
9	RF bias	This is the bias pin for RF input to Pin 10. The bias is internally provided. This pin must be ground through a capacitor.	
10	RF input	FSK-modulated RF signals from an RF amplifier are input to this pin. RF signals with up to 450MHz are acceptable.	—

Request for your special attention and precautions in using the technical information and semiconductors described in this material

- (1) An export permit needs to be obtained from the competent authorities of the Japanese Government if any of the products or technologies described in this material and controlled under the "Foreign Exchange and Foreign Trade Law" is to be exported or taken out of Japan.
- (2) The technical information described in this material is limited to showing representative characteristics and applied circuit examples of the products. It does not constitute the warranting of industrial property, the granting of relative rights, or the granting of any license.
- (3) The products described in this material are intended to be used for standard applications or general electronic equipment (such as office equipment, communications equipment, measuring instruments and household appliances).
Consult our sales staff in advance for information on the following applications:
 - Special applications (such as for airplanes, aerospace, automobiles, traffic control equipment, combustion equipment, life support systems and safety devices) in which exceptional quality and reliability are required, or if the failure or malfunction of the products may directly jeopardize life or harm the human body.
 - Any applications other than the standard applications intended.
- (4) The products and product specifications described in this material are subject to change without notice for reasons of modification and/or improvement. At the final stage of your design, purchasing, or use of the products, therefore, ask for the most up-to-date Product Standards in advance to make sure that the latest specifications satisfy your requirements.
- (5) When designing your equipment, comply with the guaranteed values, in particular those of maximum rating, the range of operating power supply voltage and heat radiation characteristics. Otherwise, we will not be liable for any defect which may arise later in your equipment.
Even when the products are used within the guaranteed values, redundant design is recommended, so that such equipment may not violate relevant laws or regulations because of the function of our products.
- (6) When using products for which dry packing is required, observe the conditions (including shelf life and after-unpacking standby time) agreed upon when specification sheets are individually exchanged.
- (7) No part of this material may be reprinted or reproduced by any means without written permission from our company.

Please read the following notes before using the datasheets

- A. These materials are intended as a reference to assist customers with the selection of Panasonic semiconductor products best suited to their applications.
Due to modification or other reasons, any information contained in this material, such as available product types, technical data, and so on, is subject to change without notice.
Customers are advised to contact our semiconductor sales office and obtain the latest information before starting precise technical research and/or purchasing activities.
- B. Panasonic is endeavoring to continually improve the quality and reliability of these materials but there is always the possibility that further rectifications will be required in the future. Therefore, Panasonic will not assume any liability for any damages arising from any errors etc. that may appear in this material.
- C. These materials are solely intended for a customer's individual use.
Therefore, without the prior written approval of Panasonic, any other use such as reproducing, selling, or distributing this material to a third party, via the Internet or in any other way, is prohibited.