






Date	SYM	REVISION RECORD	AUTH	DR.	CK.
03/09/12	D	ADDED INSULATOR OUTLINE IN PCB LAYOUT	T.B.	B.S.	
03/30/12	E	ADDED DIM. 9.19 AND 13.00	T.B.	B.S.	
11/14/14	F	UPDATED TO ROHS 2 COMPLIANT	T.B.	B.S.	



INSULATOR



SPECIFICATIONS:

- * Holder material- Polypropylene, AV161 PP, Off White
- * UL Flammability Rating: UL 94-HB File No. E108370
- * Contacts : Phosphor Bronze C5191, Nickel Plated 80-150 μ thickness
- * Vibration test: 10-50-10 hz swept in 60 seconds
x,y,z direction: 1 hour each direction
- * Result: no dislodgement of the cell or damage
no discontinuity over 10 micro-seconds
- * Shock test: half sine wave acceleration 150g.
6 micro-seconds 3 shock pulses each direction per axis,
total of 18 pulses
- * Result: no evidence of physical damage
- * ROHS 2 COMPLIANT

Tolerance (Except as noted)		Memory Protection Devices, Inc		
decimal ± .5 (.020)			Scale	Drawn By B.S.
				Approved By T.B.
Fractional ± .8 (.030)	Title CR2450 PC PINS BATTERY RETAINER WITH INSULATOR			
Angular ± 3°	Date 11/14/14	Drawing Number	BHX1-2450-PC	