

[My Cart](#)[My Part Lists](#)[Sign In/Register](#)[English \(Change\)](#)

What can we help you find?

[Products](#)[Industries](#)[Resources](#)[About TE](#)[Support Center](#)[My Account](#)

EET-0920P-4 Product Details

[Share](#)[Print](#)[Email](#)

EET-0920P-4
(1-1768018-5)

TE Internal Number: 1-1768018-5

[Active](#)

Label ID Products

[Always EU RoHS/ELV Compliant \(Statement of Compliance\)](#)

Product Highlights:

- Printer Type = Thermal Transfer
- Label Height = 9.00 mm
- Label Width = 20.00 mm
- Polyester Material
- EET Series

[View all Features](#)

Quick Links

- ▶ [Check Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)

[Add to My Part List](#)[Request Sample](#)[Find Similar Products](#)[Buy Product](#)

Documentation & Additional Information

Product Drawings:

- [EET_0920](#) (PDF, English)

Catalog Pages/Data Sheets:

- None Available

Product Specifications:

- None Available

Application Specifications:

- None Available

Instruction Sheets:

- None Available

CAD Files:

- None Available

[List all Documents](#)

Additional Information:

- [Product Line Information](#)

Related Products:

- [Tooling](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- [Material](#) = Polyester
- Series = EET
- Energy Label Type = Pressure Sensitive
- [Color](#) = Yellow

Electrical Characteristics:

- [Printer Type](#) = Thermal Transfer
- [Number of Labels Across](#) = 4
- Web Width (mm [in]) = 104.90 [4.130]

Body Features:

- Recommended Printer = TE3124
- Recommended Ribbon = TTB-110SC/300

Industry Standards:

- [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- [Lead Free Solder Processes](#) = Not relevant for lead free process
- RoHS/ELV Compliance History = Always was RoHS compliant

Printer/Label Features:

- [Label Height \(mm \[in\]\)](#) = 9.00 [0.350]
- [Label Width \(mm \[in\]\)](#) = 20.00 [0.787]
- Tamper Evident = No
- [Label Type](#) = Die-Cut
- Adhesive Type = Permanent Acrylic

Environmental:

- [Operating Temperature \(°C \[°F\]\)](#) = -40 – +150 [-40 – +302]

Conditions for Usage:

- Energy Product = Yes

Other:

- Brand = Tyco Electronics
- Comment = Alternative printers and ribbons are available for special applications.

Corporate Information

[Who We Are](#)[Investors](#)[News Room](#)[Supplier Portal](#)[Careers](#)

Quick Links

[Check Distributor Inventory](#)[Cross Reference](#)[Find Documents & Drawings](#)[Product Compliance Support Center](#)[Site Map](#)

Customer Support

[Email or Chat With Us](#)[Find a Phone Number](#)[Search Knowledge Base](#)[Manage your Account](#)

Keep Me Informed

Receive TE News, Events & Technology Updates

Enter your email address

