

SIGN	DATE	DESCRIPTION	APPROVER
	2008.06.04	Rev B: Standard material changed from UL94V-2 to UL94V-0	Jimmy
THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!			

Material

- Insulator: Nylon 66
- Flammability: UL94V-0
- Color: Ivory
- Contacts: Brass
- Plating: 120u" Tin over 30u" Nickel

Ratings

- Current: 3A
- Voltage: 250V AC(r.m.s.)
- Contact Resistance: <20 Ω
- Insulation Resistance: >1,000 Ω
- Dielectric Withstanding Voltage: 1000V AC for one minute
- Operating Temperature: -55° - +105°

RoHS Compliant




OPTIONS - add to end of p/n

G - Gold plating
BK - Black color
consult factory for other options
OPTIONS may require MOQ


PART NUMBER:

2600-XX-R



Number of circuits
02-20



(02 through 5 circuits)



(06 through 20 circuits)



Recommended P.C. Board Layout

A = 2.54 x No. of Spaces

B = A + 2.54

* Available in 02 through 20 circuits

THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF ON-SHORE TECHNOLOGY, INC. AND SHALL NOT BE REPRODUCED, COPIED OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF ON-SHORE TECHNOLOGY, INC.



TITLE	2600 Series - 2.54mm single row, right-angle friction lock header						
PART NO.	2600-XX-R			DWG NO.	2600-XX-R.DWG		
APPROVED	CHECKED	DESIGNED	DRAWN		4050	Tolerance	
	Marvin 2006.08.16	Marvin 2006.08.16	Marvin 2006.08.16		UNIT: mm/inches	X.	±0.30/.012
					SCALE: NONE	X.X	±0.20/.008
						X.XX	±0.10/.004
						X°	±1°
				SHEET: 01/01	REV: R		