







With Insulator Support



Cover



Strain Relief

Dimensions					
Positions	A	B	D	E	F
9	30.81	24.99	16.33	11.08	10.16
15	39.14	33.32	24.66	19.39	17.78
25	53.04	47.04	38.38	33.24	30.48
37	69.32	63.50	54.84	49.86	45.72

NOTES:

MATERIAL

1. Insulator Material: Glass-Filled Thermoplastic PBT, UL 94V-0, Black
2. Contact Material : Copper alloy , Gold flash selective gold
3. Shell : SPCC
4. Clinch Nut : Brass, Nickel Plated
5. Screwlock : Brass, Nickel Plated

ELECTRICAL

- 1.Current Rating : 1 AMP
- 2.Voltage Rating : 250 V AC/rms 60 Hz
- 3.Contact Resistance: 20mΩ max at 1 AMP DC
- 4.Insulation Resistance: 1000MΩ at 500 VDC
- 5.Withstand Voltage : 1000V AC/rms 60Hz for 1 minute

RoHS compliant

Unit: mm



File No.: E198287

Scale	1:1					Date	Name	Customer-No.			
TOLERANCE						Drawn	07.16.2003	Hellwig	ASSMANN WSW-No. A-DFF xx LP III/Z-UNC		
X.	±0.38					Approved	23.12.2008	Hellwig			
X.X	±0.25										
X.XX	±0.13										
DIM	TOL			23.12.2008	Dean				Drawing-No.		rev02
X.°	±3°								ASS 0128A CO		
X.X°	±1.0°	①	Drawn	16.07.2003	Hellwig						
Angle	TOL	Id.	Modification	Date	Name				Replace	Sheet	