


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.


PANDUIT PART NO.	MAX BUNDLE DIA.	PACKAGE QTY	LENGTH "L" $\pm .3$ [7]
MLT2.7WS-LP	2.7" [69]	50	10.2" [259]
MLT4WS-LP	4" [102]	50	14.3" [362]
MLT6WS-LP	6" [152]	50	20.5" [521]
MLT8WS-LP	8" [203]	50	20.8" [679]
MLT4WS-TL	4" [102]	250	14.3" [362]

B



NOTES:

1. APPLICATION TOOLS - GS4MT,PPTMT,ST2MT,ST3MT,HTMT
2. MINIMUM LOOP TENSILE STRENGTH - 200 LBS (890 NEWTONS) WHEN TESTED ON A 3" MANDREL. PART NO. MLT2.7WS-LP TESTED ON A 1 1/2" MANDREL.
3. BRACKETS [] DENOTE DIMENSIONS IN MILLIMETERS, AND ARE SHOWN FOR REFERENCE ONLY
4. TOLERANCES:
.XXX = $\pm .010$ [.25] .XX = $\pm .02$ [.5]
.X = $\pm .03$ [.8] ANGLES = $\pm 2^\circ$
5. MATERIAL: 304 STAINLESS STEEL

FULLY ROUNDED
EDGES ALONG
STRAP BODY

A

REV	DATE	BY	CHK	APR	DESCRIPTION	ECN
10A	3/13	JAMB	MIM	RGRO	UPDATE DRAWING TO NEW GLOBAL PANDUIT TITLE BLOCK WITH PANDUIT LOGO	SSECN01037
09A	1/13	JAMB	RGRO	---	ADDED PART NUMBER MLT4WS-TL TO DRAWING	-----
08A	2/12	MIM	RGRO	---	NOTE #3 METRIC DIMENSIONS NOTED AS BEING SHOWN FOR REFERENCE ONLY	-----

TITLE		WAVE-TY STANDARD SERIES 304 STAINLESS STEEL	
ITEM REVISION NAME		CUSTOMER DRAWING	
DATASET FILE NAME		N41124BS_DC/10A	
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm]		MATERIAL:	
.x $\pm .1$ [2.54] .xxx $\pm .005$ [.127] .xx $\pm .01$ [.25] ANGLES $\pm 5^\circ$		304 STAINLESS STEEL	
THIRD ANGLE PROJECTION		DRAWING NUMBER:	
N41124BS_DC		SHT 1 OF 1	
DRAWN BY		DATE	
JAMB		02/12	
CHK		SCALE	
DPN		2:1	
SIZE		A	