





PART NUMBER CODING
SWR25C-NREC-S04-ST-WH-M42


NUMBER OF POSITIONS
(CONTACTS PER ROW)



P.C.B LAYOUT



- NOTES:
1. INSULATOR MATERIAL: NYLON66, UL94V-0, COLOR: WHITE.
 2. CONTACT MATERIAL: BRASS.
 3. CONTACT PLATING: TIN OVERALL.
 4. CURRENT RATING: 4 AMPS.
 5. VOLTAGE RATING: 250V AC/DC.
 6. INSULATOR RESISTANCE: 1000 MEGOHMS MIN.
 7. CONTACT RESISTANCE: 10 MILLIOHMS MAX.
 8. DIELECTRIC WITHSTANDING VOLTAGE: 1000V AC.
 9. OPERATING TEMPERATURE: -25° C TO +85° C.
 10. MATES WITH SWH25C SERIES SINGLE ROW HOUSING.
 11. MODIFICATION: POST AT POSITION 3.



RoHS COMPLIANT


REVISIONS				
REV.	ECO. NO	DESCRIPTION	DATE	BY
A	2006	INITIAL RELEASE	9/17/09	JH

UNLESS OTHERWISE SPECIFIED:
DIMENSIONS ARE IN MM[INCHES]
TOLERANCES:
ANGULAR: ± 5°
.X= ± .3 [.01]
.XX= ± .15 [.006]
.XXX= ± .050 [.0020]
SURFACE FINISH: 63 Ra
REMOVE ALL BURRS AND SHARP EDGES .010 MAX

INTERPRET DIMENSIONS AND GEOMETRIC
TOLERANCING
PER: ANSI Y14.5M-1994

DRAWN 9/17/09 JH

THE INFORMATION HEREIN CONTAINS
PROPRIETARY INFORMATION OF
SULLINS ELECTRONICS AND IS NOT
TO BE REPRODUCED, USED OR
DISCLOSED TO OTHERS FOR ANY
PURPOSE EXCEPT AS SPECIFICALLY
AUTHORIZED IN WRITING BY AN
OFFICER OF SULLINS ELECTRONICS.



SULLINS CONNECTOR SOLUTIONS		DESCRIPTION WAFFER 2.54mm CC, 1 ROW	
PART NUMBER SWR25C-NREC-S04-ST-WH-M42		SIZE DWG. NO. C 11322	
SCALE: 6:1		REV A	
SHEET 1 OF 1			