



REV	DOCUMENT	CHANGED BY	CHECK
9	0081896	NMN 21SEP11	CMH



NOTES

- 1 - 3X 6-32 UNC X (.219) TERMINAL SCREW AND CUPWASHER
2 - TEMPERATURE RANGE: -40° F TO +160° F (-40° C TO +71° C)
3 - SEALED FOR NEMA 1, 3, 4 AND IP 66 RATING

RELEASE NO: PR-1301

CHARACTERISTICS		ELECTRICAL DATA		DESIGN UNITS: INCH			DRAWN	SRH	15MAY70		Honeywell					
OPERATING FORCE----- 15-39 OZ		CONTACT ARRANGEMENT S P D T		TOLERANCES UNLESS NOTED:			CHECK	LSD	18MAY70							
RELEASE FORCE----- 10 OZ MIN		15A-125, <u>250</u> OR 480 VAC, 2A-600 VAC -L74- 1/8 HP - 125 VAC; 1/4 HP - <u>250</u> VAC 1/2A - 125 VDC; 1/4A-250 VDC CE 1.5A, 240VAC 		NO PLACES X ± .030			THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE PERMISSION OF HONEYWELL.			TITLE SWITCH - ENCLOSED						
DIFFERENTIAL TRAVEL----- .002 MAX				ONE PLACE .X ± .015												
OVERTRAVEL----- .219 MIN				TWO PLACE .XX ± .005			INTERPRET PER ANSI Y14.5M-1982 OTHER HONEYWELL ENGINEERING STANDARDS MAY APPLY			SIZE TYPE CAGE CODE DRAWING NAME REV B I - BZV6-2RN34 9						
SWITCH-BASIC REPLACEMENT----- BZ-2RN753				THREE PLACE .XXX ± 0°												
				THIRD ANGLE PROJECTION 			RASTER			SCALE NONE WEIGHT .62LB SHEET 1 OF 1						