



www.cif.fr


MILLING DRILL BIT

Set of 5 bits

DW10.5

This document contains manufacturer's information, protected through copyright. All rights reserved. This document can not be copied, reproduced or translated without written agreement from **C.I.F**

Information contained in this document can be modified without any prior notice

CHARACTERISTICS

- **High precision milling drill bit**
- Monopiece carbide tool - Queue 3,17 mm (1/8") .
- Conical angle 90°.
- D1 : 0.1 mm
- High precision toll to mill tracks of 0,2 mm.
- Minimum rotation speed 25000 rev/ mn
- Feed rate between 4 and 7 mm/s.

UTILISATION

General use for milling on different type of PCB support such as epoxy (typical use), EMC-1, EMC-3, etc..

Isolation of 0.2 mm for a milling depth of 0.05 mm.

cif@cif.fr