



DESCRIPTION: 15 POS HIGH DENSITY OVER (2) PS/2



SPECIFICATIONS:

ELECTRICAL:

CURRENT RATING: 3 AMPS
INSULATOR RESISTANCE: 5,000 MegOHMS Min.
DIELECTRIC WITHSTANDING: 1,00VAC FOR 60SEC.
CONTACT RESISTANCE: 25MillioHMS Max.
OPERATING TEMPERATURE: -55° ~ +105° C

MATERIAL:

CONTACTS: BRASS
INSULATOR: NYLON 9T, UL94V-0
PROCESS TEMPERATURE: 230°C
HIGH DENSITY D-SUB: BLUE
MINI-DIN = LEFT PORT: PURPLE
RIGHT PORT: GREEN
SHELL: COLD ROLL STEEL


PLATING:

CONTACTS: GOLD FLASH
SHELL: NICKEL

DO NOT SCALE FROM DRAWING

	THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF NorComp AND SHALL NOT BE REPRODUCED, COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OF SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.	DRAWN: PAM JENKINS		DATE: 11-15-05	
		CHECKED:		DATE:	
NorComp	SCALE: 1 : 1		SHEET 1 OF 4		REV 7
	DWG NO. 999-H15-PS2L571				

RoHS COMPLIANT



DO NOT SCALE FROM DRAWING



THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF NorComp AND SHALL NOT BE REPRODUCED, COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OF SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.

DRAWN: PAM JENKINS

DATE: 11-15-05

CHECKED:

DATE:

SCALE: 1 : 1


SHEET 3 OF 4

REV 7

DWG NO. 999-H15-PS2L571

RoHS COMPLIANT

NorComp



DO NOT SCALE FROM DRAWING



THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF NorComp AND SHALL NOT BE REPRODUCED, COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OF SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.

DRAWN: C. SMITH		DATE: 08-31-06	
CHECKED:		DATE:	
SCALE: 2 : 1	SHEET 4	OF 4	REV 7
DWG NO. 999-H15-PS2L571			

RoHS COMPLIANT

NorComp