



Description

- Sub 1ppm performance TCXO manufactured for us by Rakon utilising their Pluto™ ASIC technology, a single chip oscillator and analogue compensation circuit operating over an extended temperature range. Its ability to function down to a supply voltage of 2.4V and low power consumption make it particularly suitable for mobile applications.

Model	CFPT-9006-1A
Model Issue number	13

Frequency Parameters

- Frequency: 10.0MHz
- Frequency Tolerance @ 25°C: INCLUSIVE
- Frequency Stability: ±1.00ppm
- Operating Temperature Range: -40.00 to 85.00°C
- Ageing:
 - ±1ppm max in 1st year, frequency ≤20MHz
 - ±3ppm max for 10 years (including the 1st year), frequency ≤20MHz
 - ±2ppm max in 1st year, frequency >20MHz
 - ±5ppm max for 10 years (including the 1st year), frequency >20MHz
- Supply Voltage Variation (±10% change): ±0.2ppm typ
- Load Variation (±5pF change): ±0.2ppm typ
- After Reflow (measured at least 60mins after reflow): ±1ppm max

Electrical Parameters

- Supply Voltage: 3.3V
- Supply Voltage Tolerance: ±10%
- Supply Current:
 - 1+Frequency(MHz)*Supply(V)*{Load(pF)+15}*10⁻³ mA
 - e.g. 20MHz, 3.3V, 15pF ≈ 2mA
- Optional reference voltage output on pad 1, suitable for potentiometer supply or DAC reference:
 - No output (standard option)
 - 2.2V for min Vs>2.4V
 - 2.7V for min Vs>3.0V

Maximum load current (mA) = Vref/10
- For manual frequency adjustment connect an external 50kΩ potentiometer between pad 1 (Reference Voltage) and pad 4 (GND) with wiper connected to pad 10 (Voltage Control). Please specify reference voltage as part of the ordering code.

Frequency Adjustment




- Input Impedance: 100kΩ min
- Modulation Bandwidth: 2kHz min
- Standard Voltage Control Ranges:
 - Without Reference Voltage Vs=3.3V 1.65V±1.0V
 - With Reference Voltage Vs=0V to Vref
- Linearity: 1% max
- B. No frequency adjustment initial calibration @ 25°C ≤ ±1.0ppm
- C. High Pulling ±10ppm to ±50ppm can be available depending on frequency and stability options (please contact an IQD Sales Office)
- Slope: Positive

Output Details

- Output Compatibility: HCMOS
- Output Load: 15pF
- Rise and Fall time (10% - 90%): 8ns max
- Duty Cycle: 45/55% max




Outline (mm)



- Pad Connections
- Vref (N/C if not required)
 - N/C
 - Do not connect
 - GND
 - Output
 - N/C
 - N/C
 - Tri-state Control (Enable)
 - +Vs
 - Voltage Control or N/C

Solder Pad Layout



Sales Office Contact Details:

UK: +44 (0)1460 270200

Germany: +49 (0)7264 9145-62

France: +33 (0)5 34 50 91 18

USA: +1 408.273.4530

Email: info@iqdfrequencyproducts.com

Web: www.iqdfrequencyproducts.com

Part No. + Packaging: **LFPTX0000001BULK**

- VoL: $<10\%$ Vs
- VoH: $>90\%$ Vs

- **Tri-state Operation:**
Logic '1' (>60% Vs) or no connection to pad 8 enables output
Logic '0' (<20% Vs) to pad 8 disables output
When at logic '0' the output stage is disabled for all output options,
but the oscillator and compensation circuit are still active (current
consumption <1mA)

- Phase Noise (typical for 13.0MHz @ 25°C):
 - 65dBc/Hz @ 1Hz
 - 95dBc/Hz @ 10Hz
 - 120dBc/Hz @ 100Hz
 - 135dBc/Hz @ 1kHz
 - 140dBc/Hz @ 10kHz
 - 145dBc/Hz @ 100kHz

- Shock: IEC 60068-2-27, Test Ea: 1500G acceleration for 0.5ms, half sine pulse, 3 shocks in each of 3 mutually perpendicular planes
- Vibration: IEC 60068-2-6, Test Fc: 10Hz-60Hz, 1.5mm displacement, 60-2000Hz at 10G, 30mins in 3 mutually perpendicular planes at 1oct/min
- Storage Temperature Range: -55 to 125°C
- Solderability: MIL-STD-202, Method 208, Category 3

- Pb-free Reflow Soldering: 260°C max for 30sec max

■ RoHS Status	Compliant
■ REACH Status	Compliant

■ Pack Type: Bulk	Loose in bulk pack
Pack Size	10
■ Alternative packing option available	

This document is correct at the time of printing; please contact your local office for the latest version.

UK: +44 (0)1460 270200
Germany: +49 (0)7264 9145-62

France: +33 (0)5 34 50 91 18
USA: +1 408.273.4530

Email: info@iqdfrequencyproducts.com
Web: www.iqdfrequencyproducts.com