






LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
DS	-		A	RELEASE	200CT2009	GC	JK
			A1	REVISED(ECR-13-012673)	05SEP2013	CH	HG
			A2	REVISED(ECR-20-007183)	19MAY2020	JH	GC
			A3	REVISED(ECR-21-103020)	07MAY2021	MJ	GC

TABLE 1. APPLICABLE TAB CONTACT.

TAB	PART NO.	WIRE RANGE(mm ²)	INSULATION DIA.(mm) (FLR)
MQS (0.64)	1355719	0.14-0.22	0.9-1.2
	928918	0.2-0.5	0.9-1.6
	963716	0.5-0.75	1.6-1.9
MCP 2.8	964292	0.2-0.5	1.15-1.6
	964294	0.5-1.0	1.4-2.1
	964296	1.25-2.5	2.2-3.0
	968946	4.0	3.4-3.7




ISO VIEW



NOTE ;

1. GENERAL TOLERANCE : ± 0.3 , $\pm 3.0^\circ$
2. APPLICABLE TAB CONTACT : SEE TABLE 1.
3. THE MATING PLUG ASS'Y P/N : 1897543
4. DELIVERY CONDITION : TPA 1'ST LOCKING.
5. DEGREE OF LEVER ASS'Y
6. CURCUIT NO.
7. MATERIAL ID MARK
- 1897540-2,1-1897540-2 : >PBT-GF15<
- 1897540-1 : >PA66-GF10<
8. APPLICATION
- 1897540-2,1-1897540-2 : FOR IN-LINE CONNECTOR
- 1897540-1 : FOR TRANSMISSION CONNECTOR

3	1897532-3	LEVER	PA66-GF35	GRAY	I			
	1897532-2		PBT-GF20	BLACK		I	I	
2	1897542-6	CAP DBL	PA66-GF10	RED	I			
	1897542-1		PBT	WHITE		I	I	
1	1-1897541-2	CAP HSG	PBT-GF15	BLACK			I	
	1897541-2		PBT-GF15	BLACK		I		
	1897541-1		PA66-GF10	NATURAL	I			
NO.	PART NO.	DESCRIPTION	MATERIAL	COLOR	Q'TY			



FULL SWING LEVER LOCATION

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm

0 PLC
1 PLC
2 PLC
3 PLC
4 PLC
ANGLES
FINISH

±
±
±
±
±
±
±

MATERIAL

-

DWN
CJ CHOI

CHK
KT LIM

APVD
HG CHO

PRODUCT SPEC

APPLICATION SPEC

WEIGHT

CUSTOMER DRAWING

TE Connectivity

NAME
HYB(MQS/MCP2.8) 22P CAP HSG ASS'Y

SIZE
A3

CAGE CODE
00779

DRAWING NO
1897540

RESTRICTED TO

SCALE
1:1

SHEET
1

OF
1

REV
A3

1470-19 (3/11)