





ダイヤルファスナー
DIAL FASTENERS

C-1127

パネル穴明け寸法
Panel drilling dimensions取付け方法
Installation method

商品番号 Product No.	RoHS 10/ CAD	製品質量(g) Mass	コード Code	単 価 Price	量販価格 Bulk Price
		数量 Quantity	単価 Price		
C-1127	2D/3D	64	21469	¥1,700	10個～ ¥1,632

●: RoHS10指令対応品

▲: RoHS10指令に対応可能です。

※大量のご注文は更にお安くなります。



特 徴 Feature

- ステンレス製で耐食性に優れています。
 - Corrosion-resistant stainless steel is used.
- 仕 様
- 材 質: つまみ/ポリアセタール(POM)
金具/ステンレス鋼板(SUS304)
 - 表面仕上: 金具/パレル研磨
- 動 作
- つまみを時計方向に回すと止め金は図示①の位置まで回転します。さらにつまみを回すと止め金はパネル側に締付けられ筐体と蓋を密着させます。
 - つまみを反時計方向に回すと止め金はパネルと反対方向に移動します。さらにつまみを回すと止め金は図示②の位置まで回転し開放となります。
- 用 途
- 密閉用筐体
- 納 期
- 標準在庫品
- Specifi-
cations
- Material: Knob: Polyacetal (POM).
Plate: Stainless steel plate (SUS304)
 - Finish: Plate: Barrel polishing
- Operation
- Turning the knob clockwise turns the stopper plate to the position Close in the figure. Further turning the knob tightens the stopper plate to the panel to close the case and cover.
 - Turning the knob counterclockwise moves the stopper plate in the direction opposite to the panel. Further tightening the knob turns the stopper plate to the position Open in the figure to open the case and cover.
- Specific use
- Airtight cases