


ST04-27F1

OUTLINE DIMENSIONS



RATINGS

● Absolute Maximum Ratings


Item	Symbol	Conditions	Ratings	Unit
Storage Temperature	T _{stg}		-55~175	°C
Junction Temperature	T _j		150	°C
Peak Surge Reverse Current	I _{RSM}	10/1000 μ s, Non-repetitive	10	A
		10/200 μ s, Non-repetitive	19	
Maximum Reverse Voltage	V _{RM}		23	V

●Electrical Characteristics (Tl=25°C)


Item	Symbol	Conditions	Ratings	Unit
Breakdown Voltage	V_{BR}	$I_R = 1\text{mA}$	24.3~29.7	V
Clamping Voltage	V_{CL}	$I_{PP} = 10\text{A}$	MAX 37	V
Reverse Current	I_R	$V_R = 23\text{V}$	MAX 5	μA

ST04-27F1

Clamping Voltage




ST04-27F1 Reverse Current




ST04-27F1


Peak Surge Reverse Current



ST04-27F1 Breakdown Voltage



ST04-27F1 Junction Capacitance



ST04-27F1 Junction Capacitance

