

## RF Power Plate Capacitors with Contoured Rim, Class 1 Ceramic



### FEATURES

- Low losses
- High reliability
- Wide range of capacitance values

### APPLICATIONS

- Induction and dielectric heating
- Antenna units
- Filter, bypass and coupling circuits

### QUICK REFERENCE DATA

| DESCRIPTION               | VALUE                          |        |        |        |                         |        |        |        |                            |        |        |        |                                |        |        |        |        |
|---------------------------|--------------------------------|--------|--------|--------|-------------------------|--------|--------|--------|----------------------------|--------|--------|--------|--------------------------------|--------|--------|--------|--------|
| Ceramic Class             | 1                              |        |        |        |                         |        |        |        |                            |        |        |        |                                |        |        |        |        |
| Ceramic Dielectric        | R7, R16, R42, R85, R230        |        |        |        | R7, R16, R42, R85, R230 |        |        |        | R7, R16, R42, R85, R230    |        |        |        | R7, R16, R42, R85, R230        |        |        |        |        |
| Type                      | PA 70, PD 70                   |        |        |        | PA 100, PD 100, PE 100  |        |        |        | PA140, PC140, PD140, PE140 |        |        |        | PA 200, PC 200, PD 200, PE 200 |        |        |        |        |
| Voltage (V <sub>p</sub> ) | 11 000                         | 12 000 | 13 000 | 14 000 | 11 000                  | 13 000 | 14 000 | 15 000 | 12 000                     | 13 000 | 14 000 | 15 000 | 16 000                         | 12 000 | 13 000 | 14 000 | 15 000 |
| Min. Capacitance (pF)     | 800                            | 80     | 120    | 25     | 1600                    | 160    | 250    | 50     | 3000                       | 600    | 300    | 100    | 3000                           | 400    | 4000   | 300    | 160    |
| Max. Capacitance (pF)     | 800                            | 600    | 500    | 300    | 1600                    | 1200   | 800    | 200    | 3000                       | 2500   | 1600   | 400    | 3000                           | 6000   | 5000   | 3000   | 800    |
| Mounting                  | Screw terminal / band terminal |        |        |        |                         |        |        |        |                            |        |        |        |                                |        |        |        |        |

### MATERIAL

Capacitor elements made from Class 1 ceramic dielectric with noble metal electrodes.

Flexible connection terminals made from copper / brass, silver plated, to allow for series and parallel interconnection

### FINISH

Noble metal electrodes and terminals are protective lacquered. The contoured insulating rim is additionally glazed

### MARKING

Type designator, capacitance value and tolerance, rated peak voltage, ceramic material code, production date code, manufacturer logo.

### ACCESSORIES ADDED

Two screws and washers (PD, PE)

### CAPACITANCE RANGE

25 pF to 6.0 nF

### CAPACITANCE TOLERANCE

< 10 pF: ± 2 pF; ± 1 pF; ± 0.5 pF

≥ 10 pF: ± 20 %; ± 10 %; ± 5 %

### CERAMIC DIELECTRIC

- R7 (TCC + 100 ppm/K)
- R16 (TCC + 100 ppm/K)
- R42 (TCC - 250 ppm/K)
- R85 (TCC - 750 ppm/K)
- R230 (TCC - 750 ppm/K)

### RATED VOLTAGE

- 11 kV<sub>p</sub>
- 12 kV<sub>p</sub>
- 13 kV<sub>p</sub>
- 14 kV<sub>p</sub>
- 15 kV<sub>p</sub>
- 16 kV<sub>p</sub>

### DIELECTRIC STRENGTH TEST

200 % of rated voltage, 50 Hz

### DISSIPATION FACTOR

R7: max. 0.07 %

R16: max. 0.04 %

R42, R85, R230: max. 0.05 %

Measuring frequencies:

1 MHz (< 1 nF); 300 kHz or 100 kHz (≥ 1 nF)

### INSULATION RESISTANCE

Min. 10 000 MΩ (at 25 °C)

### OPERATING TEMPERATURE RANGE

-55 °C to +100 °C



| SAP PART NUMBER AND ELECTRICAL DATA |         |                     |                                     |                                      |                                      |    |
|-------------------------------------|---------|---------------------|-------------------------------------|--------------------------------------|--------------------------------------|----|
| PART NUMBER                         | CERAMIC | CAP. VALUES<br>(pF) | RATED VOLTAGE<br>(kV <sub>P</sub> ) | RATED POWER <sup>(1)</sup><br>(kvar) | RATED CURRENT<br>(A <sub>RMS</sub> ) |    |
|                                     |         |                     |                                     |                                      | PD                                   | PA |
| TYPE P. 70                          |         |                     |                                     |                                      |                                      |    |
| P#0070WJ250##BF1                    | R7      | 25                  | 14                                  | 15                                   | 16                                   | 10 |
| P#0070WJ300##BF1                    |         | 30                  |                                     |                                      |                                      |    |
| P#0070WJ400##BG1                    | R16     | 40                  | 14                                  | 20                                   |                                      |    |
| P#0070WJ500##BG1                    |         | 50                  |                                     |                                      |                                      |    |
| P#0070WJ600##BG1                    |         | 60                  |                                     |                                      |                                      |    |
| P#0070WF800##BG1                    |         | 80                  |                                     |                                      |                                      |    |
| P#0070WJ101##BH1                    | R42     | 100                 | 14                                  | 20                                   |                                      |    |
| P#0070WH121##BH1                    |         | 120                 | 13                                  |                                      |                                      |    |
| P#0070WH161##BH1                    |         | 160                 |                                     |                                      |                                      |    |
| P#0070WJ201##BJ1                    | R85     | 200                 | 14                                  | 20                                   |                                      |    |
| P#0070WJ251##BJ1                    |         | 250                 |                                     |                                      |                                      |    |
| P#0070WJ301##BJ1                    |         | 300                 |                                     |                                      |                                      |    |
| P#0070WH401##BJ1                    |         | 400                 |                                     |                                      |                                      |    |
| P#0070WH501##BJ1                    |         | 500                 | 13                                  |                                      |                                      |    |
| P#0070WF601##BJ1                    |         | 600                 |                                     |                                      |                                      |    |
| P#0070WE801##BJ1                    |         | 800                 | 11                                  |                                      |                                      |    |

| SAP PART NUMBER AND ELECTRICAL DATA |         |                  |                                  |                                   |                                   |    |    |
|-------------------------------------|---------|------------------|----------------------------------|-----------------------------------|-----------------------------------|----|----|
| PART NUMBER                         | CERAMIC | CAP. VALUES (pF) | RATED VOLTAGE (kV <sub>P</sub> ) | RATED POWER <sup>(1)</sup> (kvar) | RATED CURRENT (A <sub>RMS</sub> ) |    |    |
|                                     |         |                  |                                  |                                   | PE                                | PD | PA |
| TYPE P. 100                         |         |                  |                                  |                                   |                                   |    |    |
| P#0100BJ500##BF1                    | R7      | 50               | 15                               | 30                                | 35                                | 25 | 15 |
| P#0100BJ600##BF1                    |         | 60               |                                  |                                   |                                   |    |    |
| P#0100BJ800##BG1                    | R16     | 80               | 15                               | 40                                |                                   |    |    |
| P#0100BJ101##BG1                    |         | 100              |                                  |                                   |                                   |    |    |
| P#0100BJ121##BG1                    |         | 120              |                                  |                                   |                                   |    |    |
| P#0100WH161##BG1                    |         | 160              | 13                               |                                   |                                   |    |    |
| P#0100BJ201##BH1                    | R42     | 200              | 15                               | 40                                |                                   |    |    |
| P#0100WJ251##BH1                    |         | 250              | 14                               |                                   |                                   |    |    |
| P#0100WH301##BH1                    |         | 300              | 13                               |                                   |                                   |    |    |
| P#0100WJ401##BJ1                    | R85     | 400              | 14                               | 40                                |                                   |    |    |
| P#0100WJ501##BJ1                    |         | 500              |                                  |                                   |                                   |    |    |
| P#0100WJ601##BJ1                    |         | 600              |                                  |                                   |                                   |    |    |
| P#0100WJ801##BJ1                    |         | 800              |                                  |                                   |                                   |    |    |
| P#0100WH102##BJ1                    |         | 1000             | 13                               |                                   |                                   |    |    |
| P#0100WH122##BJ1                    |         | 1200             |                                  |                                   |                                   |    |    |
| P#0100WE162##BJ1                    |         | 1600             | 11                               |                                   |                                   |    |    |

**Notes**

- # 2<sup>nd</sup> digit: code letter of terminal version A, C, D, E
- ## 14<sup>th</sup> to 15<sup>th</sup> digit: capacitance tolerance code  $\pm 20\%$  = 38;  $\pm 10\%$  = 36;  $\pm 5\%$  = 33

<sup>(1)</sup> The surface temperature during operation must not exceed +100 °C



| SAP PART NUMBER AND ELECTRICAL DATA |         |                  |                                  |                                   |                                   |     |        |
|-------------------------------------|---------|------------------|----------------------------------|-----------------------------------|-----------------------------------|-----|--------|
| PART NUMBER                         | CERAMIC | CAP. VALUES (pF) | RATED VOLTAGE (kV <sub>P</sub> ) | RATED POWER <sup>(1)</sup> (kvar) | RATED CURRENT (A <sub>RMS</sub> ) |     |        |
|                                     |         |                  |                                  |                                   | PE                                | PD  | PA, PC |
| TYPE P. 140                         |         |                  |                                  |                                   |                                   |     |        |
| P#0140BJ101##BF1                    | R7      | 100              | 15                               | 67.5                              | 45                                | 30  | 20     |
| P#0140BJ121##BF1                    |         | 120              |                                  |                                   |                                   |     |        |
| P#0140BJ161##BG1                    | R16     | 160              | 15                               | 90                                |                                   |     |        |
| P#0140BJ201##BG1                    |         | 200              |                                  |                                   |                                   |     |        |
| P#0140BJ251##BG1                    |         | 250              |                                  |                                   |                                   |     |        |
| P#0140WJ301##BG1                    |         | 300              | 14                               |                                   |                                   |     |        |
| P#0140BJ401##BH1                    | R42     | 400              | 15                               | 90                                |                                   |     |        |
| P#0140WJ501##BH1                    |         | 500              | 14                               |                                   |                                   |     |        |
| P#0140WH601##BH1                    |         | 600              | 13                               |                                   |                                   |     |        |
| P#0140WH801##BH1                    |         | 800              |                                  |                                   |                                   |     |        |
| P#0140WJ102##BJ1                    | R85     | 1000             | 14                               | 90                                |                                   |     |        |
| P#0140WJ122##BJ1                    |         | 1200             |                                  |                                   |                                   |     |        |
| P#0140WJ162##BJ1                    |         | 1600             |                                  |                                   |                                   |     |        |
| P#0140WH202##BJ1                    |         | 2000             | 13                               |                                   |                                   |     |        |
| P#0140WH252##BJ1                    |         | 2500             |                                  |                                   |                                   |     |        |
| P#0140WF302##BJ1                    |         | 3000             | 12                               |                                   |                                   |     |        |
| P#0140WL302##BK1                    | R230    | 3000             | 16                               | 90                                | 45                                | (2) | (2)    |





| SAP PART NUMBER AND ELECTRICAL DATA |         |                  |                     |                                   |                                   |    |        |
|-------------------------------------|---------|------------------|---------------------|-----------------------------------|-----------------------------------|----|--------|
| PART NUMBER                         | CERAMIC | CAP. VALUES (pF) | RATED VOLTAGE (kVp) | RATED POWER <sup>(1)</sup> (kvar) | RATED CURRENT (A <sub>RMS</sub> ) |    |        |
|                                     |         |                  |                     |                                   | PE                                | PD | PA, PC |
| TYPE P. 200                         |         |                  |                     |                                   |                                   |    |        |
| P#0200BJ161##BF1                    | R7      | 160              | 15                  | 112                               | 60                                | 40 | 25     |
| P#0200BJ201##BF1                    |         | 200              |                     |                                   |                                   |    |        |
| P#0200BJ251##BF1                    |         | 250              |                     |                                   |                                   |    |        |
| P#0200WJ301##BF1                    |         | 300              | 14                  |                                   |                                   |    |        |
| P#0200WF401##BF1                    |         | 400              | 12                  |                                   |                                   |    |        |
| P#0200BJ501##BG1                    | R16     | 500              | 15                  | 150                               |                                   |    |        |
| P#0200BJ601##BG1                    |         | 600              |                     |                                   |                                   |    |        |
| P#0200BJ801##BH1                    | R42     | 800              | 15                  | 150                               |                                   |    |        |
| P#0200WJ102##BH1                    |         | 1000             | 14                  |                                   |                                   |    |        |
| P#0200WJ122##BH1                    |         | 1200             |                     |                                   |                                   |    |        |
| P#0200WJ162##BH1                    |         | 1600             |                     |                                   |                                   |    |        |
| P#0200WJ202##BJ1                    | R85     | 2000             | 14                  | 150                               |                                   |    |        |
| P#0200WJ252##BJ1                    |         | 2500             |                     |                                   |                                   |    |        |
| P#0200WJ302##BJ1                    |         | 3000             |                     |                                   |                                   |    |        |
| P#0200WH402##BJ1                    |         | 4000             | 13                  |                                   |                                   |    |        |
| P#0200WH502##BJ1                    |         | 5000             |                     |                                   |                                   |    |        |
| P#0200WF602##BJ1                    |         | 6000             | 12                  |                                   |                                   |    |        |

**Notes**

- # 2<sup>nd</sup> digit: code letter of terminal version A, C, D, E
- ## 14<sup>th</sup> to 15<sup>th</sup> digit: capacitance tolerance code  $\pm 20\% = 38$ ;  $\pm 10\% = 36$ ;  $\pm 5\% = 33$

<sup>(1)</sup> The surface temperature during operation must not exceed +100 °C

<sup>(2)</sup> Only PE type available

**DIMENSIONS** in millimeters (inches)


| TYPE                          | PA 70<br>PD 70<br>(2)  | PA 100<br>PD 100<br>PE 100<br>(3) | PA 140<br>PD 140<br>PE 140 | PA 200<br>PC 200<br>PD 200<br>PE 200 |
|-------------------------------|------------------------|-----------------------------------|----------------------------|--------------------------------------|
| Diameter D                    | 70 ± 2 (2.76 ± 0.08)   | 100 ± 2 (3.94 ± 0.08)             | 140 ± 3 (5.51 ± 0.12)      | 200 ± 4 (7.87 ± 0.16)                |
| Thread size                   | M6                     | M8                                | M8                         | M10                                  |
| Width W <sub>1</sub>          | 35 ± 1 (1.38 ± 0.04)   | 40 ± 1 (1.58 ± 0.04)              | 40 ± 1 (1.58 ± 0.04)       | 45 ± 1 (1.77 ± 0.04)                 |
| Width W <sub>2 max.</sub> (1) | 31 (1.22)              | 31 (1.22)                         | 31 (1.22)                  | 32 (1.26)                            |
| Height H                      | -                      | -                                 | 186 ± 5 (7.32 ± 0.20)      | 246 ± 5 (9.69 ± 0.20)                |
| Length L <sub>1</sub>         | 100 ± 5 (3.94 ± 0.20)  | 145 ± 5 (5.71 ± 0.20)             | 145 ± 5 (5.71 ± 0.20)      | 255 ± 5 (10.04 ± 0.20)               |
| Length L <sub>2</sub>         | 15 ± 0.5 (0.59 ± 0.02) | 30 ± 0.5 (1.18 ± 0.02)            | 30 ± 0.5 (1.18 ± 0.02)     | 30 ± 0.5 (1.18 ± 0.02)               |

**Notes**

(1) Dimension W<sub>2</sub> will vary depending upon capacitance

(2) Types PC 70 and PE 70 are not available

(3) Type PC 100 is not available



## Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and/or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.

## Material Category Policy

**Vishay Intertechnology, Inc. hereby certifies that all its products that are identified as RoHS-Compliant fulfill the definitions and restrictions defined under Directive 2011/65/EU of The European Parliament and of the Council of June 8, 2011 on the restriction of the use of certain hazardous substances in electrical and electronic equipment (EEE) - recast, unless otherwise specified as non-compliant.**

**Please note that some Vishay documentation may still make reference to RoHS Directive 2002/95/EC. We confirm that all the products identified as being compliant to Directive 2002/95/EC conform to Directive 2011/65/EU.**

**Vishay Intertechnology, Inc. hereby certifies that all its products that are identified as Halogen-Free follow Halogen-Free requirements as per JEDEC JS709A standards. Please note that some Vishay documentation may still make reference to the IEC 61249-2-21 definition. We confirm that all the products identified as being compliant to IEC 61249-2-21 conform to JEDEC JS709A standards.**