


HDA570S-VH (High Brightness)

Dimensional Drawing

5.7" , QVGA (TFT) Color Graphics ,White LED Backlight



Features

Viewing Angle(U/D/R/L).....60/50/60/60
 High Contrast.....450
 Fast Response Time (Tr/Tf).....15/35 msec
 Built-in Controller.....none
 Touch screenoptional
 High Brightness.....700 cd/m

Physical Data

Module Size.....144.0W x104.6H x13.0T mm
 Active Area Size.....115.2W x86.4 H mm
 Dot Pitch.....0.12W x 0.36H mm
 Weight.....153g


Electrical Characteristics (VDD=3.3±0.125V 25°C)

PARAMETER	SYM	CONDITION	MIN	TYP	MAX	UNIT
OPERATING VOLTAGE	V _{DD}	-	3.0	3.3	3.6	V
OPERATING VOLTAGE	V _{LED}	I = 200 mA	-	10	-	V
INPUT HIGH VOLTAGE	V _{IH}		0.7*V _{DD}	-	V _{DD}	V
INPUT LOW VOLTAGE	V _{IL}		0	-	0.3*V _{DD}	V
OPERATING CURRENT	I _{DD}		-	50	70	mA
OPERATING CURRENT LED	I _{LED}		-	200	-	mA
POWER CONSUMPTION LED	P _D		-	165	231	mW
BRIGHTNESS	L	Average	-	700	-	cd/m ²

Pin Connections

PIN NO.	SYMBOL	FUNCTION	
1	VSS	-	Ground Pin
2	CLK	H/L	Data Sampling Clock
3	IHS	L	Horizontal Sync.
4	IVS	L	Vertical Sync.
5	VSS	-	Ground Pin
6	R0	H/L	Red Data Signal (LSB)
7	R1	H/L	Red Data Signal
8	R2	H/L	Red Data Signal
9	R3	H/L	Red Data Signal
10	R4	H/L	Red Data Signal
11	R5	H/L	Red Data Signal (MSB)
12	VSS	-	Ground Pin
13	G0	H/L	Green Data Signal (LSB)
14	G1	H/L	Green Data Signal
15	G2	H/L	Green Data Signal
16	G3	H/L	Green Data Signal
17	G4	H/L	Green Data Signal
18	G5	H/L	Green Data Signal (MSB)
19	VSS	-	Ground Pin
20	B0	H/L	Blue Data Signal (LSB)
21	B1	H/L	Blue Data Signal
22	B2	H/L	Blue Data Signal
23	B3	H/L	Blue Data Signal
24	B4	H/L	Blue Data Signal
25	B5	H/L	Blue Data Signal
26	VSS	-	Ground Pin
27	DEN	L	Data Enable Input
28	VCC	-	3.3V Power Supply
29	VCC	-	3.3V Power Supply
30	R/L	H/L	Horizontal Display Mode
31	U/D	H/L	Vertical Display Mode
32	NC	-	No Connection
33	VSS	-	Ground Pin

Power Supply




Absolute Maximum Ratings

PARAMETER	SYMBOL	MIN	MAX	UNIT
SUPPLY VOLTAGE	V _{DD} /V _{VDD}	-0.3	4.3	V
BACKLIGHT CURRENT(White LED)	I _{LED}	-	250	mA
INPUT VOLTAGE	V _{IN}	-0.3	V _{DD} + 0.3	V
OPERATING TEMPERATURE	T _{OP}	-20	+70	°C
STORAGE TEMPERATURE	T _{STG}	-30	+80	°C

HDA570S-VH (High Brightness)

Dimensional Drawing

5.7" , QVGA (TFT) Color Graphics ,White LED Backlight




HDA570ST-VH (High Brightness)

Dimensional Drawing

5.7", QVGA (TFT), with Touch Screen, White LED Backlight

TOUCH SCREEN connector : KYOCERA-ELCO 046227004100829+

With TOUCH SCREEN



HANTRONIX

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Hantronix:](#)

[HDA570ST-VH](#) [HDA570S-VH](#)