

SURFACE MOUNT SCHOTTKY BARRIER RECTIFIER

VOLTAGE RANGE 80 to 100 Volts CURRENT 1.0 Ampere

FEATURES

- * Low switching noise
- * Low forward voltage drop
- * High current capability
- * High switching capability
- * High surge capability
- * High reliability


MECHANICAL DATA

- * Case: Molded plastic
- * Epoxy: Device has UL flammability classification 94
- * Lead: MIL-STD-202E method 208C guaranteed
- * Metallurgically bonded construction
- * Mounting position: Any
- * Weight: 0.098 gram

MAXIMUM RATINGS AND ELECTRICAL CHARACTERISTICS

Ratings at 25 °C ambient temperature unless otherwise specified.
 Single phase, half wave, 60 Hz, resistive or inductive load.
 For capacitive load, derate current by 20%.

DO-214AA



Dimensions in inches and (millimeters)

MAXIMUM RATINGS (At TA = 25°C unless otherwise noted)

RATINGS	SYMBOL	FM180B	FM1100B	UNITS
Maximum Recurrent Peak Reverse Voltage	V _{RRM}	80	100	Volts
Maximum RMS Voltage	V _{RMS}	56	70	Volts
Maximum DC Blocking Voltage	V _{dc}	80	100	Volts
Maximum Average Forward Rectified Current at Derating Lead Temperature	I _O		1.0	Amps
Peak Forward Surge Current 8.3 ms single half sine-wave superimposed on rated load (JEDEC method)	I _{FSM}		40	Amps
Typical Thermal Resistance (Note 1)	R _{θJA}		57	°C/W
Typical Junction Capacitance (Note 2)	C _J		110	pF
Operating Temperature Range	T _J		150	°C
Storage Temperature Range	T _{STG}		-55 to + 150	°C

ELECTRICAL CHARACTERISTICS (At TA = 25°C unless otherwise noted)

CHARACTERISTICS	SYMBOL	FM180B	FM1100B	UNITS
Maximum Instantaneous Forward Voltage at 1.0A DC	V _F		.85	Volts
Maximum Average Reverse Current @ TA = 25°C at Rated DC Blocking Voltage	I _R		1.0	uA
@ T _J = 125°C			0.5	mA

NOTES : 1. Thermal Resistance (Junction to Ambient): Vertical PC Board Mounting, 0.5" (12.7mm) Lead Length.
 2. Measured at 1 MHz and applied reverse voltage of 4.0 volts.

2002-10

RATING AND CHARACTERISTIC CURVES (FM180B THRU FM1100B)

FIG. 1 - TYPICAL FORWARD CURRENT DERATING CURVE




FIG. 2 - TYPICAL INSTANTANEOUS FORWARD CHARACTERISTICS




FIG. 3A - TYPICAL REVERSE CHARACTERISTICS




FIG. 4 - MAXIMUM NON-REPETITIVE FORWARD SURGE CURRENT






FIG. 5 - TYPICAL JUNCTION CAPACITANCE



Mounting Pad Layout



Dimensions in inches and (millimeters)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Rectron:](#)

[FM1100L-W](#)