



REV	DOCUMENT	CHANGED BY	CHECK
A	0038670	VS 10APR08	BLR



1. TERMINALS WILL ACCEPT 6.35mm WIDE QUICK CONNECT RECEPTACLES AND COMPLY WITH EN61058-1 REQUIREMENTS.

CHARACTERISTICS		ELECTRICAL DATA		DESIGN UNITS: MM		DRAWN	KSR	01APR08	Honeywell								
CONTACT ARRANGEMENT S.P.D.T		17 CQC 16(4)A 250V~ 25T125 μ 5E4 RU® cRU® 16A 1/2HP 125/250VAC		TOLERANCES UNLESS NOTED:		CHECK	RJ	01APR08							TITLE SWITCH - BASIC		
OPERATING FORCE: 60gf MAX. DIFFERENTIAL FORCE: _____ RELEASE FORCE: 10gf MIN. FREE POSITION: _____ OPERATING POSITION: 15.3±1.5MM. PRE-TRAVEL: 3.2MM MAX. DIFFERENTIAL TRAVEL: 1.2MM MAX. OVER-TRAVEL: 1.3MM MIN. FULL OVERTRAVEL FORCE: _____				NO PLACE X ± ± ONE PLACE .X ± ± TWO PLACE .XX ± ± 0.40 THREE PLACE .XXX ± ± ANGLES X ± ± 2°		THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE PERMISSION OF HONEYWELL.			INTERPRET PER ASME Y14.5M-1994 OTHER HONEYWELL ENGINEERING STANDARDS MAY APPLY			SIZE B	TYPE I	CAGE CODE			
				THIRD ANGLE PROJECTION 		AutoCAD			SCALE	NTS			SHEET	1	OF	1	