






LOC		DIST		REVISIONS					
AD	00	P	LTR	DESCRIPTION		DATE	DWN	APVD	
			D	REVISED PER ECO-12-020314		09JUL2013	KH	DD	

⚠ MATERIAL:
HOUSING: LCP, GLASS FILLED, UL94V-0.
TERMINALS: HIGH PERFORMANCE COPPER ALLOY.

⚠ FINISH:
30μ" MIN GOLD IN CONTACT AREA. SELECTIVE TIN
ON PCB TAILS, NICKEL OVERALL.



UNGUIDED
BACKPLANE HOLE PATTERN
(CONNECTOR SIDE)



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	J. K. SHOBER	24DECT11	TE Connectivity			
		CHK	J. EABY	24DECT11				
DIMENSIONS:		APVD	J. EABY	24DECT11	NAME			
mm					IMPACT, 3 PAIR, 16 COLUMN, HEADER			
					UNGUIDED, OPEN END WALL			
					SIGNAL MODULE, 0.39 PTH			
					SIZE			
					A100779C=2007804			
MATERIAL					RESTRICTED TO			
					-			
					SCALE			
					6:1 SHEET 1 OF 2 REV D			

LOC	DIST	REVISIONS					
AD	00	P	LTR	DESCRIPTION	DATE	DWN	APVD
		-	-	SEE SHEET 1	-	-	-

	5.5	2007804-3
	4.9	2007804-2
	4.5	2007804-1
FINISH	DIM M	PART NUMBER

REFER TO WWW.TE.COM
FOR PRODUCT AVAILABILITY

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN J. K. SHOBER 24DEC11	TE Connectivity		
		CHK J. EABY 24DEC11			
DIMENSIONS:		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME	
mm		0 PLC ± 1 PLC ±0.25 2 PLC ±0.13 3 PLC ± 4 PLC ± ANGLES ± FINISH		IMPACT, 3 PAIR, 16 COLUMN, HEADER UNGUIDED, OPEN END WALL SIGNAL MODULE, 0.39 PTH	
		PRODUCT SPEC		SIZE	
		APPLICATION SPEC		CAGE CODE	
MATERIAL		WEIGHT		DRAWING NO	
-		-		A100779	
-		CUSTOMER DRAWING		©=2007804	
		SCALE		RESTRICTED TO	
		5:1		-	
		SHEET		REV	
		2		D	
		OF			
		2			