


MA4520

OUTLINE DIMENSIONS



RATINGS

●Absolute Maximum Ratings

Item	Symbol	Conditions	Ratings	Unit
Storage Temperature	Tstg		-30~125	°C
Operating Temperature	Top		-20~125	°C
Junction Temperature	Tj		150	°C
Peak Input Voltage	Vin	②+,③-,⑤-	500	V
Input Current	Iin	DC ②+,③-	5	A
		Pulse ②+,③- Duty 1/2	8	A
Maximum Power Dissipation	PD	Ta=25°C	3	W
	PD	Heatsink Tc=100°C	17	W
Dielectric Strength	Vdis	Terminals To Case AC 1 min	2	kV
Insulation Resistance		Terminals To Case 500VDC	100	MΩ
Max Voltage ④ to ⑥	V④•⑥	④+,⑥-	6	V
Max Current ⑥ to ④	I⑥•④	⑥+,④- (Peak) Duty Max 1/2	200	mA
Reverse Current	Iz	⑤+,④-	MAX 20	mA

●Electrical Characteristics (Tc=25°C)

Item	Symbol	Conditions	Ratings	Unit
Q1	Zero Gate Voltage Drain Current	Idss	MAX 250	μA
	Static Drain-Source On-State Resistance	RDS(on)	TYP (1.1)	Ω
			MAX 1.4	Ω
			MAX 2.9	°C/W
D1	Reverse Current	IR	MAX 10	μA
	Forward Voltage	VF	MAX 1.7	V
Q2	Fold Back Detection Voltage		TYP 0.7	V

●Standard Operating Condition•Design Standard For Application Circuit

Item	Conditions	Ratings	Unit
Input Rated Voltage		AC90~132	V
Output Nominal Voltage		12	V
Output Nominal Current		4	A

●Standard Operating Condition•Standard Operating Characteristics (Ta=25°C)

Item	Conditions	Ratings	Unit	
Minimum Input Full Load Output Voltage	Vin=90V, IO=4.0A	12.0±0.6	V	Fig 1, ① Refer
Maximum Input Light Load Output Voltage	Vin=132V, IO=0.40A	12.0±0.6	V	Fig 1, ② Refer
Over Current Protection	Foldback Current Vin=132V, VO=10V	MAX 6.0	A	Fig 1, ③ Refer
	Short Circuit Vin=132V, RO=0.5Ω	Nodamage To Any Device, Automatic Recovery.	—	Fig 1, ④ Refer

Figure in ○=Terminal Sign






Fig1. Output Voltage/Current

MA4520

Transfer Characteristics




MA4520 Static Drain-Source On-state Resistance




MA4520

Gate Threshold Voltage




MA4520

Capacitance




MA4520 Transient Thermal Impedance



MA4520

Safe Operating Area



MA4520

Power Derating

