


## Product Summary

$V_{(BR)DSS}$	$R_{DS(ON)}$ Max	$I_D$ Max $T_A = +25^\circ\text{C}$ (Note 5)
40V	31m $\Omega$ @ $V_{GS} = 10\text{V}$	7.0A
	50m $\Omega$ @ $V_{GS} = 4.5\text{V}$	5.6A



## Description and Applications

This MOSFET is designed to minimize the on-state resistance ( $R_{DS(ON)}$ ), yet maintain superior switching performance, making it ideal for high efficiency power management applications.

- Motor Control
- Backlighting
- Power Management Functions
- DC-DC Converters



Top View


 Top View  
 Internal Schematic


N-Channel MOSFET

N-Channel MOSFET


## Ordering Information (Note 4)

Part Number	Case	Packaging
DMN4031SSD-13	SO-8	2,500/Tape & Reel

Notes:

1. No purposely added lead. Fully EU Directive 2002/95/EC (RoHS) & 2011/65/EU (RoHS 2) compliant.
2. See [http://www.diodes.com/quality/lead\\_free.html](http://www.diodes.com/quality/lead_free.html) for more information about Diodes Incorporated's definitions of Halogen- and Antimony-free, "Green" and Lead-free.
3. Halogen- and Antimony-free "Green" products are defined as those which contain <900ppm bromine, <900ppm chlorine (<1500ppm total Br + Cl) and <1000ppm antimony compounds.
4. For packaging details, go to our website at <http://www.diodes.com/products/packages.html>.

## Marking Information



DII = Manufacturer's Marking  
 N4031SD = Product Type Marking Code  
 YYWW = Date Code Marking  
 YY or YY = Year (ex: 16 = 2016)  
 WW = Week (01 - 53)

**Maximum Ratings** (@ $T_A = +25^\circ\text{C}$ , unless otherwise specified.)

Characteristic			Symbol	Value	Units
Drain-Source Voltage			$V_{DSS}$	40	V
Gate-Source Voltage			$V_{GSS}$	$\pm 20$	V
Continuous Drain Current (Note 5) ( $V_{GS} = 10\text{V}$ )	Steady State	$T_A = +25^\circ\text{C}$ $T_A = +70^\circ\text{C}$	$I_D$	5.2 4.1	A
Continuous Drain Current (Note 5) ( $V_{GS} = 4.5\text{V}$ )	Steady State	$T_A = +25^\circ\text{C}$ $T_A = +70^\circ\text{C}$	$I_D$	4.3 3.4	A
Continuous Drain Current (Note 6) ( $V_{GS} = 10\text{V}$ )	Steady State	$T_A = +25^\circ\text{C}$ $T_A = +70^\circ\text{C}$	$I_D$	7.0 5.6	A
Continuous Drain Current (Note 6) ( $V_{GS} = 4.5\text{V}$ )	Steady State	$T_A = +25^\circ\text{C}$ $T_A = +70^\circ\text{C}$	$I_D$	5.8 4.7	A
Pulsed Drain Current (10 $\mu\text{s}$ Pulse, Duty Cycle = 1%)			$I_{DM}$	40	A
Maximum Continuous Body Diode Forward Current (Note 6)			$I_S$	2.2	A
Pulsed Body Diode Forward Current (10 $\mu\text{s}$ Pulse, Duty Cycle = 1%)			$I_{SM}$	40	A
Avalanche Current, $L = 0.1\text{mH}$ (Note 7)			$I_{AS}$	11	A
Avalanche Energy, $L = 0.1\text{mH}$ (Note 7)			$E_{AS}$	18	$\text{mJ}$

**Thermal Characteristics** (@ $T_A = +25^\circ\text{C}$ , unless otherwise specified.)







Characteristic	Symbol	Value	Units
Total Power Dissipation (Note 5)	$P_D$	1.42	W
Thermal Resistance, Junction to Ambient @ $T_A = +25^\circ\text{C}$ (Note 5)	$R_{\theta JA}$	88	$^\circ\text{C}/\text{W}$
Total Power Dissipation (Note 6)	$P_D$	2.6	W
Thermal Resistance, Junction to Ambient @ $T_A = +25^\circ\text{C}$ (Note 6)	$R_{\theta JA}$	48	$^\circ\text{C}/\text{W}$
Operating and Storage Temperature Range	$T_J, T_{STG}$	-55 to +150	$^\circ\text{C}$

**Electrical Characteristics** (@ $T_A = +25^\circ\text{C}$ , unless otherwise specified.)

Characteristic	Symbol	Min	Typ	Max	Unit	Test Condition
<b>OFF CHARACTERISTICS</b> (Note 8)						
Drain-Source Breakdown Voltage	$BV_{DSS}$	40	—	—	V	$V_{GS} = 0\text{V}, I_D = 10\text{mA}$
Zero Gate Voltage Drain Current	$I_{DSS}$	—	—	1	$\mu\text{A}$	$V_{DS} = 40\text{V}, V_{GS} = 0\text{V}$
Gate-Source Leakage	$I_{GSS}$	—	—	$\pm 100$	nA	$V_{GS} = \pm 20\text{V}, V_{DS} = 0\text{V}$
<b>ON CHARACTERISTICS</b> (Note 8)						
Gate Threshold Voltage	$V_{GS(TH)}$	1.6	2.4	3.0	V	$V_{DS} = V_{GS}, I_D = 250\mu\text{A}$
On-state drain current	$I_{D(ON)}$	20	—	—	A	$V_{GS} = 10\text{V}, V_{DS} = 5\text{A}$
Static Drain-Source On-Resistance	$R_{DS(ON)}$	—	19	31	$\text{m}\Omega$	$V_{GS} = 10\text{V}, I_D = 6\text{A}$
		—	44	50		$V_{GS} = 4.5\text{V}, I_D = 5\text{A}$
Forward Transfer Admittance	$ Y_{FS} $	—	11	—	S	$V_{DS} = 5\text{V}, I_D = 6\text{A}$
Diode Forward Voltage	$V_{SD}$	—	0.74	1.0	V	$V_{GS} = 0\text{V}, I_S = 1\text{A}$
<b>DYNAMIC CHARACTERISTICS</b> (Note 9)						
Input Capacitance	$C_{ISS}$	—	945	—	$\text{pF}$	$V_{DS} = 20\text{V}, V_{GS} = 0\text{V}, f = 1.0\text{MHz}$
Output Capacitance	$C_{OSS}$	—	69	—	$\text{pF}$	
Reverse Transfer Capacitance	$C_{RSS}$	—	58	—	$\text{pF}$	$V_{DS} = 0\text{V}, V_{GS} = 0\text{V}, f = 1.0\text{MHz}$
Gate resistance	$R_G$	—	1.45	—	$\Omega$	
Total Gate Charge ( $V_{GS} = 4.5\text{V}$ )	$Q_G$	—	8.4	—	$\text{nC}$	$V_{GS} = 10\text{V}, V_{DS} = 20\text{V}, I_D = 12\text{A}$
Total Gate Charge ( $V_{GS} = 10\text{V}$ )	$Q_G$	—	18.6	—	$\text{nC}$	
Gate-Source Charge	$Q_{GS}$	—	3.3	—	$\text{nC}$	$V_{GS} = 10\text{V}, V_{DS} = 20\text{V}, R_L = 1.6\Omega, R_G = 3\Omega$
Gate-Drain Charge	$Q_{GD}$	—	2.2	—	$\text{nC}$	
Turn-On Delay Time	$T_{D(ON)}$	—	6.4	—	ns	$V_{GS} = 10\text{V}, V_{DS} = 20\text{V}, R_L = 1.6\Omega, R_G = 3\Omega$
Turn-On Rise Time	$T_R$	—	9.7	—	ns	
Turn-Off Delay Time	$T_{D(OFF)}$	—	19.8	—	ns	
Turn-Off Fall Time	$T_F$	—	3.1	—	ns	

Notes:

5. Device mounted on FR-4 PCB, with minimum recommended pad layout. The value in any given application depends on user's specific board design
6. Device mounted on 1" x 1" FR-4PCB with high coverage 1 oz. copper, single sided.
7.  $I_{AS}$  and  $E_{AS}$  rating are based on low frequency and duty cycles to keep  $T_J = +25^\circ\text{C}$ .
8. Short duration pulse test used to minimize self-heating effect.
9. Guaranteed by design. Not subject to product testing.






Fig. 7 Gate Threshold Variation vs. Ambient Temperature




Fig. 9 Typical Junction Capacitance




Fig. 11 Gate-Charge Characteristics




Fig. 8 Diode Forward Voltage vs. Current




Fig. 10 Typical Drain-Source Leakage Current vs. Voltage




Figure 12 SOA, Safe Operation Area





Figure 13 Transient Thermal Resistance

## Package Outline Dimensions

Please see <http://www.diodes.com/package-outlines.html> for the latest version.

SO-8




SO-8			
Dim	Min	Max	Typ
<b>A</b>	1.40	1.50	1.45
<b>A1</b>	0.10	0.20	0.15
<b>b</b>	0.30	0.50	0.40
<b>c</b>	0.15	0.25	0.20
<b>D</b>	4.85	4.95	4.90
<b>E</b>	5.90	6.10	6.00
<b>E1</b>	3.80	3.90	3.85
<b>E0</b>	3.85	3.95	3.90
<b>e</b>	—	—	1.27
<b>h</b>	—	—	0.35
<b>L</b>	0.62	0.82	0.72
<b>Q</b>	0.60	0.70	0.65

All Dimensions in mm

## Suggested Pad Layout

Please see <http://www.diodes.com/package-outlines.html> for the latest version.

SO-8



Dimensions	Value (in mm)
<b>C</b>	1.27
<b>X</b>	0.802
<b>X1</b>	4.612
<b>Y</b>	1.505
<b>Y1</b>	6.50

**IMPORTANT NOTICE**

DIODES INCORPORATED MAKES NO WARRANTY OF ANY KIND, EXPRESS OR IMPLIED, WITH REGARDS TO THIS DOCUMENT, INCLUDING, BUT NOT LIMITED TO, THE IMPLIED WARRANTIES OF MERCHANTABILITY AND FITNESS FOR A PARTICULAR PURPOSE (AND THEIR EQUIVALENTS UNDER THE LAWS OF ANY JURISDICTION).

Diodes Incorporated and its subsidiaries reserve the right to make modifications, enhancements, improvements, corrections or other changes without further notice to this document and any product described herein. Diodes Incorporated does not assume any liability arising out of the application or use of this document or any product described herein; neither does Diodes Incorporated convey any license under its patent or trademark rights, nor the rights of others. Any Customer or user of this document or products described herein in such applications shall assume all risks of such use and will agree to hold Diodes Incorporated and all the companies whose products are represented on Diodes Incorporated website, harmless against all damages.

Diodes Incorporated does not warrant or accept any liability whatsoever in respect of any products purchased through unauthorized sales channel. Should Customers purchase or use Diodes Incorporated products for any unintended or unauthorized application, Customers shall indemnify and hold Diodes Incorporated and its representatives harmless against all claims, damages, expenses, and attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized application.

Products described herein may be covered by one or more United States, international or foreign patents pending. Product names and markings noted herein may also be covered by one or more United States, international or foreign trademarks.

This document is written in English but may be translated into multiple languages for reference. Only the English version of this document is the final and determinative format released by Diodes Incorporated.

**LIFE SUPPORT**

Diodes Incorporated products are specifically not authorized for use as critical components in life support devices or systems without the express written approval of the Chief Executive Officer of Diodes Incorporated. As used herein:

- A. Life support devices or systems are devices or systems which:
  1. are intended to implant into the body, or
  2. support or sustain life and whose failure to perform when properly used in accordance with instructions for use provided in the labeling can be reasonably expected to result in significant injury to the user.
- B. A critical component is any component in a life support device or system whose failure to perform can be reasonably expected to cause the failure of the life support device or to affect its safety or effectiveness.

Customers represent that they have all necessary expertise in the safety and regulatory ramifications of their life support devices or systems, and acknowledge and agree that they are solely responsible for all legal, regulatory and safety-related requirements concerning their products and any use of Diodes Incorporated products in such safety-critical, life support devices or systems, notwithstanding any devices- or systems-related information or support that may be provided by Diodes Incorporated. Further, Customers must fully indemnify Diodes Incorporated and its representatives against any damages arising out of the use of Diodes Incorporated products in such safety-critical, life support devices or systems.

Copyright © 2016, Diodes Incorporated

[www.diodes.com](http://www.diodes.com)