

För icke direkt toleranssatta mått
gäller toleransklass
General tolerances if not other-
wise stated


NOM DIM MM		TOL CLASS		
From	To	A	B	C
(1)	6	±0.05	±0.1	±0.2
(6)	30	±0.1	±0.2	±0.5
(30)	100	±0.15	±0.3	±0.8
(100)	300	±0.2	±0.5	±1.2
(300)	1000	±0.3	±0.8	±2

Hål / Holes H13

Skarpa kanter brutna där ej annat anges.
No sharp edges unless otherwise specified.


Övriga generella toleranser enligt
ritning 4100-4644.
Additional general tolerances in
accordance with drawing 4100-4644.

A - A



LASERMÄRKNING/LASER MARKING: $\triangle 2$
TEXT: Amphenol TEXTFONT SWIS721 BdOul BT
TEXTFONT: GEN-ISO
Datumkod / Date code "YYYYYY"
Serienummer / Serial number "XXXXXXX"

Rev	Change order	Change: A = Added W = Was D = Deleted	Date	Sign
2	1017750000	D 4101-3131B 4101-0068, A TEXT A 4101-2610 4101-2612 4100-6689 4101-3130B ÄNDRAD/CHANGED US PATENT NO.... W PAT PEND	031113	SE



4101-2610 $\triangle 2$
4101-2612 $\triangle 2$
4100-5200
4101-3130 B POSITION B $\triangle 2$

Packas enligt förpackningsritning 4101-2741 $\triangle 2$
Packed according to drawing 4101-2741

Förspänning/Preload 250 N ±20 N		
Tolkmått / Gauge dimensions (mm)		
Urtag Nest	Gåtolk GO	Stopptolk NO GO
Hex 4.52	Ø4.47	Ø4.57
Hex 5.41	Ø5.36	Ø5.46
Sqr 0.7	Ø0.67	Ø0.73
Hex 1.07	Ø1.04	Ø1.10
Hex 1.73	Ø1.70	Ø1.76

Material			Behandling/Treatment			Status	
Konstr./Design			Ritad/Drawn			Fristäppt	
Datum/Date			Skala/Scale			Ritn nr/Drawing no	
001117			1:1			43003042	
pressmaster®			Benämning/Denomination			Art grp	
ISO 9001			KRIMPTÅNG ACE-TOOL 3			012	
REG NR FM13687			CRIMPING TOOL			REV	
						002	