


ALL RIGHTS RESERVED. NO PORTION OF THIS PUBLICATION, WHETHER IN WHOLE OR IN PART CAN BE REPRODUCED WITHOUT THE EXPRESS WRITTEN CONSENT OF SPC TECHNOLOGY.

REVISIONS				DOC. NO. SPC-F004 * Effective: 12/21/98 * DCP No: 680					
DCP #	REV	DESCRIPTION	DRAWN	DATE	CHECKD	DATE	APPRVD	DATE	
	A	Redrawn in Autocad	JAP	12/11/91					
1199	B	Redrawn and Renamed	JWM	12/10/01	JC	12/1/01	JC	12/11/01	



NOTES:

1. Material: Electro-tin Plated Copper
2. Voltage Rating: 600V
3. Insulated Terminal Operating Temp: -40°F (-40°C) to 221°F (105°C)



OSHA
Acceptable

SPC Type No.	Wire Range (AWG)	Stud Size	W	C	L	E	Thickness	Barrel Length	Barrel I.D.	Insulator Material	Maximum Insulator Diameter	Rating	Style
CSS-DY-1406	16-14	6	.34	.29	.91	.75	.030	.25	.090	Nylon	.170	UL94V-2	3
CSS-DY-1806	22~18	6	.34	.29	.89	.73	.030	.25	.070		.145		3
CSS-DY-2204	26~24*	4	.20	.21	.61	.49	.020	.14	.030		.093		3
CSS-DY-2206	26~24*	6	.25	.28	.69	.56	.020	.13	.030		.093		3
CSS-TO-1010	12~10	10	.38	.29	.73	.54	.040	.25	.135	Non-Insulated	n/a	n/a	1
CSS-TO-1806	22~18	6	.34	.29	.70	.54	.030	.25	.070				1
CSS-TO-1808	22~18	8	.34	.29	.70	.54	.030	.25	.070				1
CSS-TO-2200	26~24*	0	.13	.12	.30	.24	.020	.13	.030				1
CSS-TO-2204	26~24*	4	.20	.21	.46	.35	.020	.14	.030				1
CSS-TO-2206	26~24*	6	.25	.28	.53	.40	.020	.13	.030				1
CSS-TV-1008	12~10	8	.38	.29	1.03	.84	.040	.25	.135	Vinyl	.250	UL94V-0	2
CSS-TV-1010	12~10	10	.38	.29	1.03	.84	.040	.25	.135		.250		2
CSS-TV-1406	16~14	6	.34	.29	.90	.74	.030	.25	.090		.170		2
CSS-TV-1408	16~14	8	.34	.29	.90	.74	.030	.25	.090		.170		2
CSS-TV-1410	16~14	10	.34	.29	.90	.74	.030	.25	.090		.170		2
CSS-TV-1806	22~18	6	.34	.29	.90	.74	.030	.25	.070		.145		2
CSS-TV-1808	22~18	8	.34	.29	.90	.74	.030	.25	.070		.145		2
CSS-TV-1810	22~18	10	.34	.29	.90	.74	.030	.25	.070		.145		2

SPC-F004.DWG

*NOT UL Listed or CSA Certified

DISCLAIMER:

ALL STATEMENTS AND TECHNICAL INFORMATION CONTAINED HEREIN ARE BASED UPON INFORMATION AND/OR TESTS WE BELIEVE TO BE ACCURATE AND RELIABLE. SINCE CONDITIONS OF USE ARE BEYOND OUR CONTROL, THE USER SHALL DETERMINE THE SUITABILITY OF THE PRODUCT FOR THE INTENDED USE AND ASSUME ALL RISK AND LIABILITY WHATSOEVER IN CONNECTION THEREWITH.



SPC TECHNOLOGY

Tolerances: Unless Otherwise Specified: .X = ±.015 .XX = ±.010 .XXX = ±.005	DRAWN BY:	DATE:	DRAWING TITLE:			
	JC	2/27/91				
	CHECKED BY:	DATE:	SIZE	DWG. NO.	ELECTRONIC FILE	REV
	JOHN COLE	12/12/91	A	TA-462	TA-462.dwg	B
	APPROVED BY:	DATE:	SCALE: NTS		U.O.M.: INCHES [mm]	SHEET: 1 OF 1
	John Liszka	12/12/91				