






F E D A I	95.10 [3.744]	24	5-641208-4
	91.14 [3.588]	23	5-641208-3
	87.17 [3.432]	22	5-641208-2
	83.21 [3.276]	21	5-641208-1
	79.25 [3.120]	20	5-641208-0
	75.29 [2.964]	19	4-641208-9
	71.32 [2.808]	18	4-641208-8
	67.36 [2.652]	17	4-641208-7
	63.40 [2.496]	16	4-641208-6
	59.44 [2.340]	15	4-641208-5
	55.47 [2.184]	14	4-641208-4
	51.51 [2.028]	13	4-641208-3
	47.55 [1.872]	12	4-641208-2
	43.59 [1.716]	11	4-641208-1
	39.62 [1.560]	10	4-641208-0
	35.66 [1.404]	9	3-641208-9
	31.70 [1.248]	8	3-641208-8
	27.74 [1.092]	7	3-641208-7
	23.77 [.936]	6	3-641208-6
	19.81 [.780]	5	3-641208-5
15.85 [.624]	4	3-641208-4	
11.89 [.468]	3	3-641208-3	
7.92 [.312]	2	3-641208-2	
DIM (L)		NO.OF POSN	ASSEMBLY

CONTAINERS LEAD	95.10 [3.744]	24	2-641208-4	
	91.14 [3.588]	23	2-641208-3	
	87.17 [3.432]	22	2-641208-2	
	83.21 [3.276]	21	2-641208-1	
	79.25 [3.120]	20	2-641208-0	
	75.29 [2.964]	19	1-641208-9	
	71.32 [2.808]	18	1-641208-8	
	67.36 [2.652]	17	1-641208-7	
	63.40 [2.496]	16	1-641208-6	
	59.44 [2.340]	15	1-641208-5	
	55.47 [2.184]	14	1-641208-4	
	51.51 [2.028]	13	1-641208-3	
	47.55 [1.872]	12	1-641208-2	
	43.59 [1.716]	11	1-641208-1	
	39.62 [1.560]	10	1-641208-0	
	35.66 [1.404]	9	641208-9	
	31.70 [1.248]	8	641208-8	
	27.74 [1.092]	7	641208-7	
	23.77 [.936]	6	641208-6	
	19.81 [.780]	5	641208-5	
	15.85 [.624]	4	641208-4	
	11.89 [.468]	3	641208-3	
	7.92 [.312]	2	641208-2	
	DIM (L)	NO.OF POSN	ASSEMBLY	

METRIC

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN S. HOOVER 07-Nov-2002 CHK D. BOSSI 07-Nov-2002 APP'D D. BOSSI 07-Nov-2002	 TE Connectivity		
DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 P/LC ± 1 P/LC ± 2 P/LC ± 0.13 [0.005] 3 P/LC ± 4 P/LC ± ANGLES ± FINISH		NAME MTA-156 HEADER ASSEMBLY, FRICTION LOCK, STRAIGHT, .045 SQUARE POST, .000030 GOLD	
		PRODUCT SPEC		SIZE A1	
		APPLICATION SPEC			
MATERIAL 		WEIGHT		DRAWING NO 00779	
		CUSTOMER DRAWING		RESTRICTED TO -	
		SCALE 5:1		SHEET 1 OF 1	
		REV AC			