



LOC		DIST		REVISIONS			
GP	00	P	LYR	DESCRIPTION	DATE	OWN	APVD
				D1	REVISED PER ECO-11-005027	10MAY2011	RK HMR





- 1 MATERIAL: COPPER ALLOY.
- 2 FINISH: TIN PLATING PER ASTM B 545, 1.25μm MINIMUM THICKNESS
ALL OVER NICKEL FLASH PER QQ-N-290. NONPLATED EDGES PERMISSIBLE.
- 3 PADS AND VIAS CHASSIS GROUND.
- 4 DATUM AND BASIC DIMENSIONS ESTABLISHED BY CUSTOMER.
- 5 REFERENCE APPLICATION SPEC 114-13120, HOLE A, FOR RECOMMENDED
DRILL HOLE DIAMETER AND PLATING THICKNESSES.
- 6 COMPANY LOGO IN APPROXIMATE AREA SHOWN




1761014-1
1X2 CAGE ASSEMBLY
SCALE 4:1

1 x 2 CAGE	1761014-1
DESCRIPTION	PART NO

THIS DRAWING IS A CONTROLLED DOCUMENT.			OWN VAN SCYOC 15MAR2004	 TE Connectivity	
DIMENSIONS:			CHK M J PHILLIPS 15MAR2004		
mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME	ASSEMBLY, CAGE, IX2 PRESS FIT, SFP
		0 PLC ± 2 PLC ±0.10 3 PLC ± 4 PLC ± ANGLES ±0°			
MATERIAL		FINISH		PRODUCT SPEC	RESTRICTED TO
1		2		108-1950	
				APPLICATION SPEC	SIZE
				114-13120	CAGE CODE
				WEIGHT	DRAWING NO
				CUSTOMER DRAWING	A100779C=1761014
				SCALE	4:1
				SHEET	1 OF 2
				REV	D





LOC		DIST		REVISES			
GP	00	P	LYR	DESCRIPTION	DATE	OWN	APVD
		-	-	SEE SHEET 1	-	-	-

THIS DRAWING IS A CONTROLLED DOCUMENT.		OWN W. VAN SCYOC 15MAR2004	NAME		ASSEMBLY, CAGE, 1X2 PRESS FIT, SFP		
DIMENSIONS: mm		CHK MJ PHILLIPS 15MAR2004					
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD MJ PHILLIPS 15MAR2004	PRODUCT SPEC		SIZE CAGE CODE DRAWING NO		
9 PLC ±		108-1950		APPLICATION SPEC		RESTRICTED TO	
3 PLC ±0.10		114-13120		WEIGHT		SCALE 4:1 SHEET 2 OF 2 REV D1	
5 PLC ±		CUSTOMER DRAWING					
4 PLC ±							
ANGLES ±2°0'							
FINISH							

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1761014-1](#)