

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0530481210](#)
Status: **Active**
Overview:
Description: 1.25mm (.049") Pitch PicoBlade™ Header, Right Angle, 12 Circuits

Documents:
[3D Model](#) [Product Specification PS-51021-010 \(PDF\)](#)
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)


General
Product Family PCB Headers
Series [53048](#)
Application Wire-to-Board
Overview PicoBlade™;
Product Name PicoBlade™

Physical
Breakaway No
Circuits (Loaded) 12
Circuits (maximum) 12
Color - Resin Natural
First Mate / Last Break No
Glow-Wire Compliant No
Guide to Mating Part No
Keying to Mating Part None
Lock to Mating Part Yes
Mated Height (in) 0.138 In
Mated Height (mm) 3.50 mm
Material - Plating Mating Tin
Material - Resin Nylon
Number of Rows 1
Orientation Right Angle
PC Tail Length (in) 0.091 In
PC Tail Length (mm) 2.30 mm
PCB Locator No
PCB Retention None
PCB Thickness Recommended (in) 0.031 In
PCB Thickness Recommended (mm) 0.80 mm
Packaging Type Tray
Pitch - Mating Interface (in) 0.049 In
Pitch - Mating Interface (mm) 1.25 mm
Polarized to PCB No
Shrouded Fully
Stackable No
Temperature Range - Operating -40°C to +85°C
Termination Interface: Style Through Hole

Electrical
Current - Maximum 1A
Voltage - Maximum 125V

Material Info

Reference - Drawing Numbers
Product Specification PS-51021-010
Product Specification RPS-51021-007
Product Specification RPS-51021-011
Product Specification RPS-51021-048



EU RoHS
ELV and RoHS
Compliant
REACH SVHC
Not Reviewed
Halogen-Free
Status
Not Reviewed



Need more information on product environmental compliance?
Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series
[53048](#) Series

Mates With
[51021](#) PicoBlade™ Wire-to-Wire

Product Specification
Product Specification
Product Specification
Product Specification
Sales Drawing

RPS-51021-059
RPS-51021-060
RPS-51021-071
RPS-51021-089
SD-53048-**10

This document was generated on 11/05/2009

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION